

RF Inductor-Wirewound

Automotive



AWS25JRF0-KIT JIS 2520 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω) Max.	IDC(mA)Max.	Quantity
AWCS0029282110NJ00	2.9	2.7	2.1	2520/1008	10	5	0.08	1000	20
AWCS0029282112NJ00	2.9	2.7	2.1	2520/1008	12	5	0.09	1000	20
AWCS0029282115NJ00	2.9	2.7	2.1	2520/1008	15	5	0.1	1000	20
AWCS0029282118NJ00	2.9	2.7	2.1	2520/1008	18	5	0.11	1000	20
AWCS0029282122NJ00	2.9	2.7	2.1	2520/1008	22	5	0.12	1000	20
AWCS0029282127NJ00	2.9	2.7	2.1	2520/1008	27	5	0.13	1000	20
AWCS0029282133NJ00	2.9	2.7	2.1	2520/1008	33	5	0.14	1000	20
AWCS0029282139NJ00	2.9	2.7	2.1	2520/1008	39	5	0.15	1000	20
AWCS0029282147NJ00	2.9	2.7	2.1	2520/1008	47	5	0.16	1000	20
AWCS0029282156NJ00	2.9	2.7	2.1	2520/1008	56	5	0.18	1000	20
AWCS0029282168NJ00	2.9	2.7	2.1	2520/1008	68	5	0.2	1000	20
AWCS0029282182NJ00	2.9	2.7	2.1	2520/1008	82	5	0.22	1000	20
AWCS00292821R10J00	2.9	2.7	2.1	2520/1008	100	5	0.56	650	20
AWCS00292821R12J00	2.9	2.7	2.1	2520/1008	120	5	0.63	650	20
AWCS00292821R15J00	2.9	2.7	2.1	2520/1008	150	5	0.7	580	20
AWCS00292821R18J00	2.9	2.7	2.1	2520/1008	180	5	0.77	620	20
AWCS00292821R20J00	2.9	2.7	2.1	2520/1008	200	5	0.84	500	20
AWCS00292821R22J00	2.9	2.7	2.1	2520/1008	220	5	0.84	500	20
AWCS00292821R27J00	2.9	2.7	2.1	2520/1008	270	5	0.91	500	20
AWCS00292821R33J00	2.9	2.7	2.1	2520/1008	330	5	1.05	450	20
AWCS00292821R39J00	2.9	2.7	2.1	2520/1008	390	5	1.12	470	20
AWCS00292821R47J00	2.9	2.7	2.1	2520/1008	470	5	1.19	470	20
AWCS00292821R56J00	2.9	2.7	2.1	2520/1008	560	5	1.33	400	20
AWCS00292821R62J00	2.9	2.7	2.1	2520/1008	620	5	1.4	300	20
AWCS00292821R68J00	2.9	2.7	2.1	2520/1008	680	5	1.47	400	20
AWCS00292821R75J00	2.9	2.7	2.1	2520/1008	750	5	1.54	360	20
AWCS00292821R82J00	2.9	2.7	2.1	2520/1008	820	5	1.61	400	20
AWCS00292821R91J00	2.9	2.7	2.1	2520/1008	910	5	1.68	380	20

RF Inductor-Wirewound

Automotive



AWS25JRF0-KIT JIS 2520 Size

Dimensions – Millimeters (Inches)

2520

