

**RoHS
Compliant**

Description

This is digital high-voltage insulation resistance tester, designed with multiple ranges including 250V, 500V, 1000V, 2500V. It is an ideal measurement meter for electric power, telecommunication, meteorology, machine room, oil field, electromechanical installation and maintenance, and power supply department of Industry and mining enterprise.

Features

- Output voltage range: Up to 2.5KV
- PI/DAR measurement
- Short circuit current measurement
- Automatic leakage current display
- Stepping voltage: 10% of the range
- High voltage alarm
- Automatic discharge
- Data storage: 999 set
- PC software analysis: via USB cable
- Overvoltage category: CAT IV 600V



Specifications

Rated voltage	MP701119
250V	0.25MΩ~4.99GΩ, 5GΩ~24.9GΩ, 25GΩ~100GΩ
500V	<0.5MΩ, 0.5MΩ~9.99GΩ, 10GΩ~49.9GΩ, 50GΩ~200GΩ
1000V	<1MΩ, 1MΩ~19.9GΩ, 20GΩ~99.9GΩ, 100GΩ~400GΩ
2500V	<2.5MΩ, 2.0MΩ~49.9GΩ, 50GΩ~249GΩ, 250GΩ~1TΩ
Capacitance test	NA
Low resistor test	NA
Output voltage (Ratng)	stepping voltage range
250V	350V, 275V, 300V
500V	300V, 350V, 400V, 450V, 500V, 550V, 600V
1000V	500V, 600V, 700V, 800V, 900V, 1000V, 1100V, 1200V
2500V	1250V, 1500V, 1750V, 2000V, 2250V, 2500V
DC voltage	30~1000V DC
AC voltage	30~750V AC 50Hz/60Hz
Current	0.01nA~3.5mA
Short-circuit current	about 3.5mA
PI test	automtic display
DAR test	automatic display
Timing measurement	√
Resistance comparison	√
Monitoring functon	Monitor the voltage of measured object and the discharge state after testing. If voltage is higher than 36V, it is forbidden to test for protecting the tester and the operator

Insulation Tester

multicomp PRO

Timer testing	Record testing time automatically. Timing range: 0s~99m and 59s
Storage function	999 sets
Data transmission	Upload testing data to computer via USB cable.
Low battery indication	√
Auto power off	N/A
Dimensions	238mm × 166mm × 90.5mm
CAT rating	CAT IV 600V
General Characteristics	
Power supply	8 x LR14 Alkaline battery
Product colour	Black+Red
Product weight	About 1800g (including battery)
Accessories	User manual 1 pc; Test lead (red, black, green: 1 for each) 3 pcs; USB cable 1 pc; Lithium battery charger (Output: 16.8Vdc, 2A) 1 pc (UT512E only); Lithium battery pack (14.8V, 5200mAh) 1 pc (UT512E only); Adapting charging stand (optional, model: UT-W12, for UT512E only); 8 PCS LR14 alkaline batteries (UT512D); Carrying strap 1pc
Standard package	case + carton
size	238mm × 166mm × 90.5mm (L × W × D)

Part Number Table

Description	Part Number
Insulation Resistance Tester, 2.5kV	MP701119

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO