

Selector Switch

multicomp PRO



**RoHS
Compliant**




Specifications

Mechanical life	: >500,000 operations
Electrical life	: >100,000 operations
Electrical durability	: 1,000,000 cycles AC-15, 230V/1.6A 1,000,000 cycles DC-13, 24V/0.6A
Rate insulation voltage	: 400V
Rated thermal current	: 8A
Contact resistance	: 100mΩ max. (at 1A 6-8V DC)
Insulation resistance	: 100MΩ min. (at 500V DC)
Dielectric strength	: 2000V AC 50/60 HZ for 1 min
Degree of protection	: IP66, Type 4X Indoor use only & Type 13 IP IP30 (under panel)
Storage temperature	: -40°C to +85°C
Operating temperature	: -25°C to +70°C
Operating humidity	: 45% to 85% RH
Wire diameter	: 16~26 AWG, 0.2~1.5mm ²
Stripping length	: 8mm


Diagram



M12 B-code 4pin



A



Part Number Table

Description	Part Number
Selector Switch, Black, 2 Position, 1 NO	MPCP2S-2E10

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO