

DK1F3EA222M86RBH01



Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Mobile Electronics, Medical equipment [GHTE A/B/C] except for implant equipment, Automotive infotainment/comfort equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.


Notices

X1/Y1 Class Certified Products. Rated Voltage
X1:440Vac(r.m.s.)/1500Vdc Y1:300Vac(r.m.s.)/1500Vdc

References

Packaging	Specifications	Standard Packing Quantity
R	330Embossed Tape	2500

Appearance & Shape



Mass (typ.)	
1 piece	0.29g

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DK1F3EA222M86RBH01



Specifications

Length	11.4±0.5mm
Width	6.0±0.5mm
Thickness	2.5mm max.
Capacitance	2200pF ±20%
Metal terminal width e	0.75±0.3mm
Operating Temperature Range	-40°C to 125°C
Rated Voltage	300Vac(r.m.s.)
Capacitance change rate	+30/-80%
Temperature characteristics (complied standard)	F(JIS)
Temperature range of temperature characteristics	-25°C to 85°C

Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DK1F3EA222M86RBH01




Characteristic Data


The charts below may show another part number which shares its characteristics.




DK1F3EA222M86RBH01 |Z| DCOV, 20degC



DK1F3EA222M86RBH01 R DCOV, 20degC



DK1F3EA222M86RBH01 C-DC bias capchange, 20.0




DK1F3EA222M86RBH01 C-AC Voltage capchange, I


Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DK1F3EA222M86RBH01



DK1F3EA222M86RBH01 C-Temp. capchange, DCOV,



DK1F3EA222M86RBH01 S21 DCOV, 20degC

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.