



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

## Specifications

<b>Type</b>	3.5 mm Passive Voltage
<b>Bandwidth</b>	500 MHz
<b>Attenuation</b>	10x
<b>Input Impedance</b>	10 megaohms
<b>Input Capacitance</b>	8 pF
<b>Output Impedance</b>	1 megaohms
<b>Risetime</b>	0.7 ns
<b>IEC Rating</b>	300 V CAT II
<b>Compensation</b>	818 pF
<b>Cable Length</b>	1.3 m
<b>Readout Actuator</b>	Yes
<b>Operating Temperature (degrees)</b>	-10 to +55C
<b>Humidity</b>	85% RH or less (at 35 C)
<b>RoHS (2011/65/EU)</b>	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

