

CT3290RA-PRO

3.5 mm Compact Oscilloscope Probe


500 MHz, 35 mm Compact Probe, 10x, cable length 13...

Description

One of Cal Test highest frequency passive probe at 500 MHz.

This compact probe is an excellent replacement for probes used with high frequency scopes. Complete accessories supplied with this model.

TheCT3667 is an accessory for theCT3290RA.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

Type	3.5 mm Passive Voltage
Bandwidth	500 MHz
Attenuation	10x
Input Impedance	10 megaohms
Input Capacitance	8 pF
Output Impedance	1 megaohms
Risetime	0.7 ns
IEC Rating	300 V CAT II
Compensation	818 pF
Cable Length	1.3 m
Readout Actuator	Yes
Operating Temperature (degrees)	-10 to +55C
Humidity	85% RH or less (at 35 C)
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

