



Part Number : [2034560003](#)

Product Description : Mirror Mezz Hermaphroditic Connector, 5.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs

Series Number : 203456

Status : Active

Product Category : Board-to-Board Connectors

---

## Documents & Resources

### Drawings

[Drawing 2034560003\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 2034560003\\_stp.zip](#)

[Electrical Model Document 2043581506EE-000.pdf](#)

[S-Parameter Model 2043581506SP-000.zip](#)

### Specifications


[Application Specification 2028280001-AS-000.pdf](#)

[Product Specification 2028280001-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Board-to-Board Connectors
Series	203456
Description	Mirror Mezz Hermaphroditic Connector, 5.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs
Application	Board-to-Board
Component Type	PCB Header
Product Family	Mirror Mezz Connectors
Product Name	Mirror Mezz
UPC	191128393010

### Electrical

Current - Maximum per Contact	0.75A (1 Oz Cu Trace), 1.2A (2 Oz Cu Trace)
Voltage - Maximum	30V AC (RMS)/DC

### Physical

Breakaway	No
Circuits (Loaded)	699
Circuits (maximum)	699
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None

Lock to Mating Part	No
Mated Height	11.00mm
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	11.343/g
Number of Rows	11
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	1.50mm, 4.00mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	BGA Solder

### Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
Mirror Mezz Hermaphroditic Connector, 2.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs	<u>2048430001</u>

Mirror Mezz Hermaphroditic Connectors	<u>203456</u>
Mates With	This is a hermaphroditic, self-mating part.

---

This document was generated on Jul 30, 2024