



Bulk Metal® Foil Technology High Precision, Current Sensing, Power Surface Mount Resistor with Wrap-Around Terminals with Rated Power up to 4 W and TCR ± 10 ppm/°C

FEATURES

- Temperature coefficient of resistance (TCR): 10 ppm/°C max. (-55°C to +125°C, +25°C ref.)
- Power rating: to 4 W
- Resistance tolerance: to $\pm 0.1\%$
- Resistance range: 40 m Ω to 500 m Ω
- Load-life stability: to $\pm 0.03\%$ Maximum (70°C, 2000 h at rated power)
- Short-time overload: 0.01% Maximum
- Power coefficient of resistance (PCR), “ ΔR due to self heating”: 5 ppm/W at rated power
- Electrostatic discharge (ESD): up to 25 kV
- Solderable terminations
- Terminal finish available: lead (Pb)-free, tin/lead alloy
- Quick prototype quantities available; please contact foil@vpgsensors.com



Four terminal (Kelvin) design:
allows for precise and accurate measurements.

INTRODUCTION

Model FRCS3637 is a surface mount chip resistor designed with 4 pads for Kelvin connection. Utilizing Bulk Metal® Foil as the resistance element, it provides enhanced characteristic capabilities resulting in superior performance when compared with other resistor technologies. The unique combination of Z Foil technology along with the designed 4-pad wrap-around terminals provides high reliability of solder mounting connections.

Figure 1 – Power Derating Curve




Table 1 – Specifications

Parameter	Value
Resistance range	40 m Ω to 500 m Ω
Power rating at 70°C	up to 4 W
Maximum current	$(P / R)^{1/2}$
Tolerance	to $\pm 0.1\%$
Temperature coefficient maximum (-55°C to +125°C, +25°C Ref.)	± 10 ppm/°C ⁽²⁾
Operating temperature range	-65°C to +170°C
Maximum working voltage	$(P \times R)^{1/2}$
Notes	
⁽¹⁾ Contact application engineering for values outside this range.	
⁽²⁾ For tighter TCR, please contact application engineering: foil@vpgsensors.com .	

Note


* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS compliant. Please see the information/tables in this datasheet for details.

THE KEY APPLICATIONS

Applications requiring accuracy and repeatability under stress conditions such as the following:

- Switching and linear power supplies
- Precision current-sensing
- Power management systems
- Feedback circuits
- Power amplifiers
- Measurement instrumentation
- Battery Management
- Medical and automatic test equipment
- Satellites and aerospace systems
- Commercial and Military avionics
- Test and measurement equipment
- Electronic scales

Figure 2—Dimensions and Land Pattern in Inches (Millimeters)




Dimensions – Tolerances ±0.010 (±0.254)					
L	W	H	T	A	B
0.365 (9.271)	0.370 (9.398)	0.028 (0.711)	0.091 (2.311)	0.058 (1.473)	0.040 (1.016)
Land Pattern Dimensions – Tolerances ±0.003 (±0.076)					
a	b	c	d	e	
0.116 (2.95)	0.390 (9.91)	0.066 (1.68)	0.024 (0.610)	0.178 (4.52)	

Table 3—Performance Specifications

Test/Condition	MIL-PRF-49465B ΔR LIMITS	Typical ΔR Limits ⁽¹⁾	Max ΔR Limits ⁽¹⁾
Thermal shock -65°C to +150°C, 5 cycles, 15 min at each extreme	±(0.5% +0.0005R)	0.01%	0.02%
Load-life stability 2000h, +70°C at rated power of 3 W terminals temperature 150°C	±(1.0% +0.0005R)	0.02%	0.03%
Load-life stability 2000h, +70°C at working power of 4 W terminals temperature 170°C		0.03%	0.05%
Short-time overload 15 W, 5 s 20 W, 5 s	±(0.5% +0.0005R)	0.005% 0.02%	0.01% 0.05%
High temperature exposure 1000 h, 170°C	±(1.0% +0.0005R)	0.02%	0.05%
Moisture resistance MIL-STD-202, method 106, 0 power	±(0.5% +0.0005R)	0.01%	0.02%
Shock 100 g, 6 ms, 5 pulses	±(0.1% +0.0005R)	0.05%	0.01%
Vibration High Frequency 10-2,000 Hz, 20g Discontinuity 0.1ms	±(0.1% +0.0005R)	0.05%	0.01%
Low Temperature Storage -55°C for 24 h	±(0.5% +0.0005R)	0.003%	0.005%
Low Temperature Operation -65°C, 45 min. at 3W	±(0.2% +0.0005R)	0.005%	0.01%

Note
⁽¹⁾ Measurement error allowed for ΔR limits: 0.0005 Ω.

Figures 3—Global Part Number Information⁽¹⁾



Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.