


COAXIAL ADAPTER, TNC-precision, 50 Ohm, Bulkhead, jack / jack (female / female)

34_TNC-50-0-4/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
TNC-precision	jack (female)	IEC 60169-17_MIL-STD-348A/406_CECC 22200
TNC-precision	jack (female)	IEC 60169-17_MIL-STD-348A/406_CECC 22200

Interface and material data		
TNC-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
TNC-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

COAXIAL ADAPTER, TNC-precision, 50 Ohm, Bulkhead, jack / jack (female / female)

34_TNC-50-0-4/133_N

Electrical data		
Impedance	50 Ω	
Interface frequency	18 GHz	
VSWR	DC - 8 GHz ($\leq 1.07 + 0.01 f$ GHz)	
Mechanical data		
Weight	0.0191 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-65 °C ... 125 °C	
Ordering Information Table		
Item number	Item description	Packaging type
22658794	34_TNC-50-0-4/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2079 / Date of publication: 27.05.2024 / uncontrolled copy