

5221123-2 ✓ ACTIVE

TE Internal #: 5221123-2

BNC RF Interface, Jack, 50 Ω , Bayonet, 4 GHz Operating


Frequency, Cable-to-Board, 1 Position, Printed Circuit Board, Board

Mount

[View on TE.com >](#)



Connectors > RF Connectors > Coax Connectors > BNC Vertical Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism



RF Interface: **BNC**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Bayonet**

[All BNC Vertical Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism \(30\)](#)

Features

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	-------------

Body Features

Body Material	Zinc
---------------	------

Body Plating Material	Tin-Lead
-----------------------	----------

Contact Features

RF Connector Center Contact Underplating Material	Copper, Nickel
	1080 μ m
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Phosphor Bronze

Termination Features

Termination Post & Tail Length	4.83 mm[.19 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

Profile Height from PCB	15.88 mm[.625 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Grade	Commercial
Dielectric Material	VALOX

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2024
(240)Candidate List Declared Against: JAN 2024
(240)

SVHC > Threshold:

Pb (4% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE

TE Part # CAT-076-BNCJKISG50
BNC RF Connector: Jack Assembly,
Isolated Ground Protection, 50 Ohm

TE

TE Part # CAT-076-BNCJKSH50
BNC RF Connector: jack assembly -
short, 50 Ohm, 4Ghz

TE

TE Part # 5413771-3
JACK BLKHD,COML BNC,HEX CRIMP

TE

TE Part # 1-5227079-6
COMM BNC PLUG

TE

TE Part # 5413779-3
COML BNC,50 OHM, HEX CRIMPTE Part # 5227169-5
BNC - SOLDER RECEPTTE Part # 5227169-7
BNC SOLDER JACK RECEPTACLETE Part # 5227169-8
BNC - SOLDER RECEPT




TE Part # 5228979-7
JACK,COML,SERIES BNC,GOLD PL



TE Part # 5228980-7
JACK,BHD,COML,SERIES BNC,GOLD



TE Part # 1-5221128-7
PLUG,COMMERCIAL BNC



TE Part # 5227079-5
COMM BNC PLUG



TE Part # 5227079-6
COMM. BNC-PLUG



TE Part # 8-5227079-2
COMM BNC PLUG



TE Part # 1-5227079-1
COMM BNC PLUG



TE Part # 228979-7
JACK,COML,SERIES BNC,GOLD PL



TE Part # 413779-3
COML BNC,50 OHM, HEX CRIMP



TE Part # 2016080-2
JACK,PCB,COMMERCIAL BNC



TE Part # 228979-6
JACK,COML,SERIES BNC,GOLD PL



TE Part # 414265-3
PLUG, TWIST ON, COML BNC

Customers Also Bought



TE Part #1-5747150-3
09 RCPT SP/FMS SCRLK




TE Part #5499141-3
A/L UNIV HDR 16P RA LG LAT



TE Part #1-640550-2
Polyester PCB Connector Covers: 2.54 mm, MTA 100



TE Part #1-640456-2
12P MTA100 HDR ASSY F/L SQ STR



TE Part #640551-5
05P MTA156 COVER



TE Part #2-382811-1
SHUNT, ECON, PHBRSN, BLACK



TE Part #350760-4
03P UMNL HDR ASSY PC



TE Part #104257-8
09 MTE RCPT HSG SR LATCH .100



Documents

Product Drawings

[JACK,PCB,VERT,COMMERCIAL BNC](#)

English

CAD Files

[3D PDF](#)

English

[Customer View Model](#)

[ENG_CVM_5221123-2_O.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_5221123-2_O.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_5221123-2_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BNC Connectors](#)

English

Product Specifications

[Product Specification](#)

English

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English