

1-963725-1 ✓ ACTIVE

TE Internal #: 1-963725-1

TE Internal Description: MQS PIN CONTACT

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1452426-1
EXTRACTION TOOL



TE Part # 6-1579007-1
EXTRACTION TOOL



TE Part # 6-928918-1
MQS0,63 Sn tab LL unseal. 0,2-0,35

Customers Also Bought



TE Part #1-968699-1
2POS MQS TAB COD A



TE Part #1355717-1
MQS0,63 Sn rec LL unseal. 0,08-0,22



TE Part #710030-5
XCT 16-8



TE Part #1765813001
FLHTC0311-0.35-2




TE Part #1SNA125118R1300
M6/8.N



TE Part #963728-1
MQS PIN CONTACT SWS



TE Part #963730-1
MQS PIN CONTACT WITH SPRING



TE Part #2295408-1
47POS MIXED MQS REC COD A

Documents

CAD Files

Customer View Model

[ENG_CVM_1-963725-1_C9.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-963725-1_C9.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-963725-1_C9.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-963725-1_W.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-963725-1_W.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-963725-1_W.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



[Product Specifications](#)

[Application Specification](#)

English