



Connectors > Lighting Connectors > LED Holders



Lighting Connector Features Included: **Does Not Enable Zhaga Compatibility, No Thermal Protection, Not Dimmable, Not Programmable, No Driver on Board**

Operating Voltage: **300 VDC**

Termination Method to Wire & Cable: **Poke-In**

Connector System: **Wire-to-Component**

Number of Positions: **2**

Features

Configuration Features

Lighting Connector Features Included	Does Not Enable Zhaga Compatibility, No Thermal Protection, Not Dimmable, Not Programmable, No Driver on Board
Number of Positions	2

Electrical Characteristics

Operating Voltage	300 VDC
-------------------	---------

Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Product Type Features

Connector System	Wire-to-Component
Connector & Contact Terminates To	Printed Circuit Board
COB Substrate Thickness	1 mm

Contact Features

--	--



Contact Current Rating (Max)	5 A
------------------------------	-----

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
--------------------	-----------

EU ELV Compliance	Compliant
-------------------	-----------

Body Features

Compatible LED	Nichia NFDWJ130B-V2, Nichia NFCLJ108B, Nichia NFCWJ108B, Nichia NFDLJ130B, Nichia NFDWJ130B
----------------	---------------------------------------------------------------------------------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
----------------------------------------	--------------------------------------------------------------------------------------------------------------------------------

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	-------------------------------------------------------------------------------------

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--------------------------------------------

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | LUMAWISE LED Holders



Customers Also Bought



Documents

Product Drawings

[LUMAWISE LED HOLDER Z50 LOW PROFILE 1924](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2213580-1_C.2d_dxf.zip](#)

English



Customer View Model

[ENG_CVM_CVM_2213580-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213580-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LUMAWISE LED Holders for Nichia J flyer](#)

[LUMAWISE LED Holders for Nichia J Series COB](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

Agency Approvals

[CB_CERT_IEC_60838-2-2_NL-42967_C1](#)

English