



Connectors > Connector Accessories > Connector Backshells > DEUTSCH DT Backshells



Connector Backshell Product Type: **Backshell**

Primary Product Material: **PA GF**

Number of Positions: **4**

Sealable: **No**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

[All DEUTSCH DT Backshells \(47\)](#)

Features

Industry Standards

IP Rating	IP6K9K
UL Flammability Rating	UL 94HB

Dimensions

Compatible Cable Diameter Range	6 – 10 mm [.236 – .394 in]
---------------------------------	----------------------------

Packaging Features

Packaging Method	Box
Packaging Quantity	500

Other

Serviceable	Yes
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Usage Conditions

Operating Temperature (Max)	125 °C [257 °F]
-----------------------------	-----------------



Operating Temperature Range

-55 – 125 °C[-67 – 257 °F]

Body Features

Primary Product Color	Black
Primary Product Material	PA GF

Product Type Features

Connector Backshell Product Type	Backshell
Sealable	No

Configuration Features

Number of Positions	4
---------------------	---

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # DT-RT1
EXT TOOL, FRONT RELEASE

TE Part # CAT-J41-DDPC
DEUTSCH DT Plug Connectors

TE Part # 1011-264-0405
BKSHL, 4P, BLK, PLG,RA,NW6/7.5/8.5 /10

TE Part # CAT-D487-CH8172
DEUTSCH DT Series Housings & Connectors

TE Part # CAT-J41-DDCC
DEUTSCH DT Color Connectors

Also in the Series

DEUTSCH DT

Automotive Connector Caps & Covers
(19)

Automotive Housings(738)

Connector Caps & Covers(1)

Connector Strain Relief(31)

Rectangular Backshells & Clamps(3)

Customers Also Bought

TE Part #CAT-AL8-KSTS081
Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever

TE Part #1870533001
100G0121-0.25-0/9

TE Part #1-2141846-2
CARRIER,RECEPTACLE HSG, 25POS, ASSY

TE Part #7-1415033-1
SR6ZA024





TE Part #1028-017-0005

ADPTR, BKSHL, 6,8P, BLK, RA, NW 10 /13



TE Part #CAT-R21-652T79

Single Wall ZH 150: Heat Shrink Tubing, 2:1 Shrink Ratio

TE Part #A81929-000

HX-SCE-3.2-50-4

TE Part #A04570-000

HX-SCE-6.4-50-4

Documents

Product Drawings

BKSHL, 4P, BLK, PLG, RA, NW6/7.5/8.5/10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1011-236-0405_99_c-1011-236-0405-99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1011-236-0405_99_c-1011-236-0405-99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1011-236-0405_99_c-1011-236-0405-99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

TERMINALS AND CONNECTORS

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English