

Agastat

TE Internal #: 5-1423159-4

Time Delay Relay, DC, 2 Form C DPDT-CO, 10 A Contact Rating,
Panel Mount, 75 °C [167 °F][View on TE.com >](#)

Relays & Contactors > Electromechanical Relays

Relay & Contactor Type: **Time Delay Relay**Current Type: **DC**Contact Arrangement: **2 Form C DPDT-CO**Contact Current Rating: **10 A**Main Termination & Connection Type: **Screw Terminals**

Features

Product Type Features

Relay & Contactor Type	Time Delay Relay
------------------------	------------------

Configuration Features

Relay Options	Hardware and Adjustment for Horizontal Operation
Contact Arrangement	2 Form C DPDT-CO

Electrical Characteristics

Input Voltage	250 VDC
Contact Current Rating	10 A

Termination Features

Main Termination & Connection Type	Screw Terminals
Coil Termination & Connection Type	Screw Terminals

Mechanical Attachment

Product Mounting Feature Type	Flange with Mounting Holes
Product Mount Type	Panel Mount

Dimensions

Product Width	65.2 mm[2.57 in]
Product Length	71.88 mm[2.83 in]
Product Height	126.74 mm[4.99 in]

Usage Conditions

Operating Temperature Range	-30 – 75 °C
Environmental Ambient Temperature (Max)	75 °C[167 °F]

Operation/Application

Type of Control	Knob
Delay Time	1 – 10 minutes
Mode of Operation	On-Delay
Repeatability (Max)	±10%
Current Type	DC

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2-1423157-4
7012AK=RLY,STD,ON,2P,120VAC,30

Customers Also Bought



TE Part #1-1393118-4
KUP-14D15-24=KU-



TE Part #193844-1
PIN ASSY. 14 AWG



TE Part #6-1393246-5
W23-X1A1G-10=W23/W31



TE Part #601967-1
CRIMPING TOOL M22520/1-01



TE Part #632692-000
GELCAP-3(B5)



TE Part #9-1415018-1
SR6A4110 - V23050-A1110-A533




TE Part #193846-1
SKT ASSY.



TE Part #9-1393211-3
T92S11D22-12



TE Part #1-601967-6
POSITIONER TYPE II CONTACTS



TE Part #1-601967-5
POSITIONER TYPE II CONTACTS

Documents

Product Drawings

7012SFX=RLY,STD,ON,2P,250VDC,

English

Datasheets & Catalog Pages

5-1773450-5_sec12_7000

English