



Tango 49

2G/3G/4G 96mm length panel mount antenna



Key Features

- Whip style panel mounting
- All 4G frequencies
- 2G and 3G frequency coverage

General Description

The Tango 49 is strong slim antenna ideally suited to mounting remotely from the device to maximise signal strength and can also be mounted directly into alarm / control panels.

For its comparatively small size the antenna has a good peak gain of 2dBi and omni directional radiation.

Supplied as standard with an SMA male connector and 2.5m of cable. The antenna can be supplied with alternative cable lengths or connector types for volume orders.

Additional Considerations

- Extremely versatile for global location
- Strong but slim antenna





Tango 49

2G/3G/4G 96mm length panel mount antenna


Electrical Specifications

Temperature Range:	-45°C - +75°C
Impedance:	50 Ohm
Peak Gain:	2.16dBi
VSWR:	<3:1
Frequency Range:	698 - 960MHz 1710 - 2600 MHz
Polarization:	Vertical

Mechanical Specifications

Dimensions:	L96 x 28mm Ø
Connector:	SMA
Cable:	RG174
Mounting Method:	M12 15mm Stud
Max recommended material thickness:	7mm

VSWR






Tango 49

2G/3G/4G 96mm length panel mount antenna

Bracket Drawing



Ordering Details

Part Number	Description
TANGO49/2.5M/SMAM/S/S/17	2G/3G/4G 96mm length panel mount antenna