



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	B HEIGHT	IMPRINT AREA C	VERTICAL REPEAT D	LABELS PER ROW	STANDARD PKG. QTY.
S050X075VA1Y	GMV3	0.750 [19.0]	0.25 +/- .050 [6.35]	1.000 [25.4]	8	5000
S050X125VA1Y	GMV3	1.250 [31.8]	0.38 +/- .050 [9.53]	1.500 [38.1]	8	5000
S050X150VA1Y	GMV3	1.500 [38.1]	0.50 +/- .050 [12.7]	1.800 [45.7]	8	5000



UNWIND
DIRECTION

- NOTES:
 1. MILLIMETER ARE IN [].
 2. SEE MFG. DRAWING NO. A61153.

CAD FILENAME/LAYERS
 I00472DG_C10195_S050XxxxVA1x_04.PRT

PANDUIT CORP TINLEY PARK, ILLINOIS

CUSTOMER DRAWING OPTIMUM SELF-LAM.
 S050X***VA1Y
 THERMAL TRANSFER PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ± .050
 (.XX) ± .032 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN IN
 INCHES, THIRD ANGLE PROJECTION

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
4	4/8/08	RVU		OBSOLETE P/N: S050X075VA1, S050X125VA1, and S050X150VA1. GMV3 WAS GMV. Tol. INCREASED.	5390	R		
3	5/4/07	RVU		[38.1] WAS [12.7].	4973	R		
2	8-30-06	RVU		ADDED PART NO. S050X075VA1Y, S050X125VA1Y AND S050X150VA1Y.	4678	R		
1	3-30-06	RVU		38.1 mm WAS 12.7 mm.	4431	R		
0	9-22-04	RVU		DRAWING RELEASED.		R		

DRAWN BY
 RVU
 DATE
 9-22-04
 CHK'D

MAT'L:
 SEE TABLE

SCALE
 NTS
 DRAWING NO.
 C10195
 DWG
 SIZE