Industry

HCB • HCN

Hanging scale

Go to back page of catalogue

Order Hotline:

Delivery 1 day

Best buy ≥ 3 pcs.

OPTION

DKD

+4 days

KERN HCB






Standard




CAL Adjusting program (CAL): For quick setting of the balance's accuracy. External adjusting weight required.



Weighing units: can be switched to e.g. non-metric units at the touch of a key. See balance



type of protection is shown by the pictogram. For a definition see the glossary, page 96.



Animal weighing program:



strong vibrations are filtered out.

INOX Stainless steel: the balance is



Battery operation:

The battery type is specified for each device.



TAR Tare: put back displayed value to "0" during weighing process, e.g. to add or remove weighing material from a container.

Convenient for hanging loads

KERN HCB+HCN Hanging scale

STANDARD

Both models:



included, stainless steel with safety catch, aperture 15 mm. Can be reordered,

KERN HCB-A01

Multi data hold function √ By pressing the Hold key

- · weight display can be "frozen" for 5 sec
- weight display can be "frozen" until any key is pressed
- / when the weighing value remains unchanged
- · the weight display is automatically "frozen for 5 sec
- · the weight display is automatically "frozen" until any key is pressed

LCD display

digit height 12 mm

Peak load display (Peak Hold)

displays the highest load value (peak load) of a weighing, measuring frequency 5 Hz



Ready for use Batteries included.

HCB: Size AA (2 x 1.5 V). Operating time approx. 300h. HCN: Size AA (2 x 1.5 V), Operating time approx. 200h. AUTO-OFF function after 3 min without a change of load to preserve the batteries, can be switched off

S-hook stainless steel, included. Aperture approx. 25 mm. Can be reordered, HCB-A02



Model	Weighing Read-					OPTI	OPTION	
KERN	range Max kg	out				Certifi- cate KERN	DKD	
HCB 20K10	20	10				963-128		
HCB 20K50	20	50				963-128		
HCB 50K20	50	20				963-128		
HCB 50K100	50	100				963-128		
HCB 99K50	99	50				963-129		
HCB 100K200	100	200				963-129		
HCB 200K100	200	100				963-129		
HCB 200K500	200	500				963-129		
	stainless steel							
HCN 20K50IP	20	50				963-128		
HCN 50K100IP	50	100				963-128		
HCN 100K200IP	100	200				963-129		
HCN 200K500IP	200	500				963-129		



KERN HCB Housing, plastic WxDxH 80x45x150 mm, Total height with snap link and S-hook 290 mm. Net weight approx, 400 g. KERN HCN Housing, stainless steel WxDxH 95x55x175 mm. Total height with snap link and S-hook 315 mm. Net weight approx. 1.5 kg.

KERN – Your DKD-Calibration Partner

issues DKD calibration certificates for balances and test weights in its own accredited laboratories. It is internationally valid. KERN is a manufacturer of test weights in the international classes of accuracy

E1, E2, F1, F2, M1, M2, M3, from 1 mg up to 2000 kg

DKD = German
Calibration Service



Your KERN specialist dealer