


## PT 1,5/ 4-PH-3,5

Order No.: 1984332

The figure shows a 10-position version of the product

<http://eshop.phoenixcontact.net/phoenix/treeViewClick.do?UID=1984332>

Plug component, Nominal current: 8 A, Nom. voltage: 160 V, Pitch:  
3.5 mm, Number of positions: 4, Connection type: Screw connection,  
Color: green

| Commercial data          |                    |
|--------------------------|--------------------|
| EAN                      | 4017918935894      |
| Pack                     | 250 pcs.           |
| Customs tariff           | 85369010           |
| Weight/Piece             | 0.002783 KG        |
| Catalog page information | Page 471 (CC-2009) |

### Product notes

WEEE/RoHS-compliant since:  
01/01/2003



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### Dimensions / positions

|             |         |
|-------------|---------|
| Length      | 12.9 mm |
| Height      | 11 mm   |
| Pitch       | 3.5 mm  |
| Dimension a | 10.5 mm |

|                        |         |
|------------------------|---------|
| Number of positions    | 4       |
| Screw thread           | M2      |
| Tightening torque, min | 0.22 Nm |
| Tightening torque max  | 0.25 Nm |

**Technical data**

|                                    |                     |
|------------------------------------|---------------------|
| Insulating material group          | I                   |
| Rated surge voltage (III/3)        | 2.5 kV              |
| Rated surge voltage (III/2)        | 2.5 kV              |
| Rated surge voltage (II/2)         | 2.5 kV              |
| Rated voltage (III/2)              | 200 V               |
| Rated voltage (II/2)               | 400 V               |
| Connection in acc. with standard   | EN-VDE              |
| Nominal current $I_N$              | 8 A                 |
| Nominal voltage $U_N$              | 160 V               |
| Nominal cross section              | 1.5 mm <sup>2</sup> |
| Maximum load current               | 8 A                 |
| Insulating material                | PA                  |
| Inflammability class acc. to UL 94 | V0                  |
| Stripping length                   | 5 mm                |

**Connection data**

|   |                      |
|---|----------------------|
| Conductor cross section solid min.                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.                                      | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded min.                                   | 0.2 mm <sup>2</sup>  |
| Conductor cross section stranded max.                                   | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max. | 0.75 mm <sup>2</sup> |
| Conductor cross section AWG/kcmil min.                                  | 26                   |
| Conductor cross section AWG/kcmil max                                   | 16                   |
| 2 conductors with same cross section, solid min.                        | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid max.                        | 0.34 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded min.                     | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded max.                     | 0.5 mm <sup>2</sup>  |

**Certificates / Approvals**



Certification CCA, CUL, SEV, UL

**CUL**

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 10 A  |
| AWG/kcmil             | 26-16 |

**UL**


|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 10 A  |
| AWG/kcmil             | 26-16 |

**Accessories**

| Item    | Designation | Description  |
|---------|-------------|--|
| 1205037 | SZS 0,4X2,5 | Screwdriver, bladed, matches all screw terminal blocks up to 1.5 mm <sup>2</sup> connection cross section, blade: 0.4 x 2.5 mm |


**Diagrams/Drawings**

Diagram



Dimensioned drawing

---



**Address**

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 00  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>



© 2010 Phoenix Contact  
Technical modifications reserved;