

Microsoft® Wireless Mobile Mouse 3000



Version Information	
Product Name	Microsoft® Wireless Mobile Mouse 3000
Product Version	Microsoft Wireless Mobile Mouse 3000 v1.0
Mouse Version	Microsoft Wireless Mobile Mouse 3000 v1.0
Transceiver Version	Microsoft Notebook Receiver v2.0
Product Dimensions	
Mouse Length	3.76 inches (95.4 millimeters)
Mouse Width	2.21 inches (56.2 millimeters)
Mouse Depth/Height	1.59 inches (40.3 millimeters)
Mouse Weight	3.17 ounces (90 grams) includes 1 AA alkaline battery; typical battery weight may vary
Transceiver Length	2.61 inches (66.3 millimeters)
Transceiver Width	0.84 inches (21.3 millimeters)
Transceiver Depth/Height	0.36 inches (9.22 millimeters)
Transceiver Weight	0.32 ounces (9.1 grams)
Compatibility and Localization	
Interface	USB 2.0 Compatible
Operating Systems	<ul style="list-style-type: none"> Microsoft Windows® Vista™ and Windows XP with Service Pack 2 (SP2) Macintosh Mac OS X v10.2-10.5
Top-line System Requirements	<p>For Windows-based PC:</p> <ul style="list-style-type: none"> Requires a PC that meets the requirements for and has installed one of these operating systems: Windows Vista or Windows XP with Service Pack 2 (SP2) 100 MB Hard Drive USB Port CD-ROM Drive IntelliPoint software version 6.3 <p>For Macintosh:</p> <ul style="list-style-type: none"> Mac OS X v10.2-10.5* 30 MB Hard Drive IntelliPoint for Mac software version 6.3 <p>Internet access may be required for certain features. Local and/or long distance telephone charges may apply.</p> <p>* If you are using Macintosh OS X, the Magnifier enlarges text and images on the entire screen.</p>
Compatibility Logos	<ul style="list-style-type: none"> Certified for Microsoft Windows Vista Mac logo Universal Mac logo Certified USB logo
Software Localization	<p>For a Microsoft Windows-based PC:</p> <p>Microsoft IntelliPoint software may be installed in Simplified Chinese, Traditional Chinese, English, French, German, Italian, Japanese, Korean, Brazilian Portuguese, Iberian Portuguese, or Spanish. If available, standard setup will install the software in the default OS language. Otherwise, the English language version will be installed.</p> <p>For a Macintosh PC:</p> <p>Microsoft IntelliPoint for Mac will install in English, French, German, Italian, Japanese, Brazilian Portuguese, and Spanish. User settings for OS language preference determine which localized version of the software is displayed. In the event that OS language preferences are not supported, the English language version will be displayed.</p>
Tracking Technology	
Mouse Tracking System	Microsoft-proprietary high-definition optical technology
Imaging Rate	Dynamically adaptable to 6000 frames per second
X-Y Resolution	1000 points per inch (39.4 points per millimeter)
Tracking Speed	Up to 20 inches (508 millimeters) per second
Wireless Technology	
Wireless Platform	27 MHz Radio Frequency (RF)
Wireless Channels	27.045 MHz Channel 0 and 27.145 MHz Channel 1
Wireless IDs	65,000 random identification codes
Wireless Range	3.5 feet (1.07 meters) typical.** Note: RF range is affected by many factors, such as nearby metallic objects and relative positioning of the keyboard, mouse, and receiver. And lower wireless range implemented in SKUs produced for sale in the Republic of Korea to support compliance with RF range configured to 2.2 feet typical.
Product Feature Performance	
Mouse Button Features	4 buttons including scroll wheel button
Mobility Features	Snap-in receiver turns mouse off, conserving battery life
Right & Left Button Life	3,000,000 actuations at no more than 4 actuations per second
Side Button Life	1,000,000 actuations at no more than 4 actuations per second
Wheel Button Life	250,000 actuations at no more than 4 actuations per second
Mouse Scrolling Features	Tilt wheel enables vertical and horizontal scrolling
Wheel Vertical Scrolling Life	<ul style="list-style-type: none"> 85,000 revolutions (away from user) 300,000 revolutions (towards user)
Storage Temperature & Humidity	-40 °F (-40 °C) to 140 °F (60 °C) at <5% to 65% relative humidity (non-condensing)
Operating Temperature & Humidity	32 °F (0 °C) to 104 °F (40 °C) at <5% to 80% relative humidity (non-condensing)
Power Requirements	
Battery Type and Quantity	1 AA alkaline battery (included)
Battery Life	6 months typical
Certification Information	
Country of Manufacture	People's Republic of China (PRC)
ISO 9001 Qualified Manufacturer	Yes
ISO 14001 Qualified Manufacturer	Yes
FCC ID	This device complies with part 15 of the FCC Rules and Industry Canada RSS-210. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC standards. For home and office use. 1359, Wireless Mobile Mouse 3000 v1.0 and 1051, Notebook Receiver v2.0 FCC IDs: C3K1359 and C3K1051.
Agency and Regulatory Marks	<ul style="list-style-type: none"> FCC Declaration of Conformity (USA) UL and cUL Listed Accessory (USA and Canada) RSS-310 and ICES-003 report on file (Canada) Anatel Certificate (Brazil) R&TTE Declaration of Conformity, Safety and EMC (European Union) TUV-GS Certificate (EU, Germany) ACAM/ED Declaration of Conformity (Australia and New Zealand) ICASA Certificate (South Africa) GOST Certificate (Russia) VCCI Certificate (Japan) BSMI and DGT Certificates (Taiwan) MIC Certificate (Korea) CMIJ Certificate (China) SQAS Certificate (Malaysia) IDA Approval (Singapore) CB Scheme Certificate (International) SASO Registration (Kingdom of Saudi Arabia) POSTEL Certificate (Indonesia) NTC Certificate (Philippines) CNC Certificate (Argentina) TEC Certificate (India) NTC SDcC (Thailand) NTRA Cert (Egypt) TRA Certificate (Africa)
Windows Hardware Quality Labs (WHQL)	ID: PENDING Microsoft Windows XP (x86, x64) and Windows Vista (x86, x64)

** Mouse lower wireless range implemented in SKUs produced for sale in the Republic of Korea to support compliance to requirements documented in Article 6 of Assessment Decree of Radio Wave Act, Conformity Assessment Procedure for Type Official Approval and Type Registration of Radio Equipment (RRL Notice 2006-128), and Technical Requirements for the Radio Equipment for other services than Broadcasting, Marine, Aeronaut (RRL Notice 2005-127) of the Republic of Korea

* Mouse 2.2 feet (0.67 meters) typical.

Results stated herein are based on internal Microsoft testing. Individual results and performance may vary. Any device images shown are not actual size. This document is provided for informational purposes only and is subject to change without notice. Microsoft makes no warranty, express or implied, with this document or the information contained herein. Review any public use or publications of any data herein with your local legal counsel.