



Helagaine Braided Sleeving

Features and Benefits

Helagaine HLB polyester braided sleeving has an expansion ratio of 3:1. With diameters running from 5 mm to 54 mm, just 3 sizes of the versatile Helagaine HLB covers a very wide range of applications. Large differences in diameter, for instance due to cable jacks and connectors, are easy to handle.

The sleeves are supplied in practical 10m reels in dispenser boxes. The boxes protect the sleeves and can be efficiently stocked. The dispenser opening also guarantees easy extraction of the sleeves.

Application


Helagaine HLB is supplied in practical dispenser boxes and covers a wide range of applications with only a few sizes. It is ideal for both the professional and the home user. Helagaine HLB bundles and effectively protects cables and wires, for instance in HiFi systems and in industrial plants. Helagaine HLB also provides good resistance to abrasion.

Application Method

To prevent fraying, the sleeve is cut with a hot-cutting tool, which melts and cleanly fuses the ends of the yarn



Helagaine HLB: The expansion rate makes it possible. Only three sizes in a handy dispenser box for almost all standard diameters.



Helagaine HLB covers a wide range of applications with only three sizes.



For more information on the HSG0 hot-cutting tool, please turn to page 274.

Material Data

| | |
|-----------------------|--|
| Material | Polyester (PET) |
| Colour | Black (BK) |
| Operating Temperature | -50 °C to +150 °C, Intermittent +200 °C |
| Melting Point | +250 °C |
| Oxygen Index | 34 % (NF G 07-128) |



Technical Table

| Article-No. | Type | Ø D | Bundle Ø min. | Bundle Ø max. | Reel Length (m) |
|-------------|--------------|-----|---------------|---------------|-----------------|
| 170-80150 | HLB15 | 15 | 5 | 21 | 10 |
| 170-80250 | HLB25 | 25 | 10 | 30 | 10 |
| 170-80350 | HLB35 | 35 | 18 | 54 | 10 |

All dimensions in mm. Subject to technical changes.