












7 Fuse Terminal Blocks 6 mm² /AWG 10, Series 282

36

<p>0.2 – 6 mm² 500 V/6 kV/3 max. ① 10 A max. ①</p> <p>Terminal block width 13 mm / 0.512 in  12 – 13 mm / 0.49 in</p> <p>*   </p>	<p>AWG 24 – 10 600 V, 10 A ①  250 V, 10 A ① </p> <p>Terminal block width 13 mm / 0.512 in  12 – 13 mm / 0.49 in</p> <p>*   </p>
--	---












① 500 V = rated voltage
 6 kV = rated surge voltage
 3 = pollution degree
 (see also section 15)
 Nominal voltage and current are given by the LED or fuse
 Technical details see pages 7.38 – 7.39



Description	Item No.	Pack. unit pcs	Item No.	Pack. unit pcs
Fuse terminal block , for DIN 35 rail, for cartridges	Fuse terminal block , without indicator grey, 5 x 20 mm	282-122 40	Fuse terminal blocks , without indicator grey, 1/4" x 1"	282-120 40
			grey, 1/4" x 1 1/4"	282-128 40

Accessories

Appropriate marking system **WMB/WSB** (see section 14)

	End and intermediate plate orange grey	4 mm / 0.157 in thick orange grey	282-312 282-311	50 (2 x 25) 50 (2 x 25)	4 mm / 0.157 in thick orange grey	282-312 282-311	50 (2 x 25) 50 (2 x 25)
	Screwless end stop , for DIN 35 rail	6 mm / 0.236 in wide 10 mm / 0.394 in wide	249-116 249-117	100 (4 x 25) 50 (2 x 25)	6 mm / 0.236 in wide 10 mm / 0.394 in wide	249-116 249-117	100 (4 x 25) 50 (2 x 25)
	Adjacent jumper , insulated	I _N 41 A grey	282-402	100 (4 x 25)	I _N 41 A grey	282-402	100 (4 x 25)
	Test plug adapter , suitable for terminal blocks 1.5 mm ² – 10 mm ² /AWG 16 – 8	8 mm / 0.315 in wide for test plug 4 mm / 0.157 in Ø	209-170	50 (2 x 25)	8 mm / 0.315 in wide for test plug 4 mm / 0.157 in Ø	209-170	50 (2 x 25)
	Test plug , 6 mm / 0.236 in wide, with CAGE CLAMP® for 0.08 mm ² - 2.5 mm ² /AWG 28 - 14	I _N 24 A	281-407	100 (4 x 25)	I _N 24 A	281-407	100 (4 x 25)
	Miniature metric fuse , 5 x 20 mm, without indicator, 6.3 A / 250 V, medium slow		282-451	200 (20 x 10)			
	Miniature metric fuse , 5 x 25 mm, with indicator, 6.3 A / 250 V, medium slow						
	Miniature metric fuse , 5 x 25 mm, with indicator, 10 A / 450 V, quick acting						
	Miniature fuse , 1/4" x 1", without indicator, 10 A / 240 V, acc. to BS 1362					282-458	200 (20 x 10)
	Miniature fuse , 1/4" x 1 1/4", without indicator, 10 A / 250 V, medium slow					282-457	200 (20 x 10)
	Miniature fuse , 1/4" x 1 1/4", without indicator, 10 A / 500 V, very quick acting					282-454	200 (20 x 10)

* For further approvals with corresponding ratings see section 15.