

935153521410-xxT

There can be several part numbers depending on packing configurations and electrode surface materials. Please see the following part numbers for standard products of this item.


935153521410-T3T, 935153521410-T5T, 935153521410-W0T, 935153521410-F1T

In Production

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Medical equipment [GHTF A/B], Medical equipment [GHTF C], Mobile Electronics, Mobile Communication, Consumer Electronics - Differential Transmission, HDD, Double feed detection Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Optical Module, Broadband communication

Appearance & Shape



Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

935153521410-xxT

Features

- | Ultra large band performance higher than 26GHz
- | Resonance free and phase stability
- | Unique capacitance value of 1nF in 0101
- | High stability of capacitance value over temperature, voltage and aging
- | Ultra low ESR and ESL and high reliability
- | Compatible with standard wire bonding assembly (ball and wedge)
(please refer to our Assembly Application Note for more details)


Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

935153521410-xxT



Specifications

Series	UWSC
Applications	Broadband,Power Amp for RF
Features	High Frequency
Mounting Method	Wire-bonding vertical
Operating Temperature Range	-55°C to 150°C
Size Code (in inch)	0202
L x W (size)	0.50 x 0.50mm
Frequency	26GHz+
Breakdown Voltage (For the rated voltage, please see the FAQ.)	150Vdc
Capacitance	1nF
Thickness	250µm

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.