
### **DISCRETE SEMICONDUCTORS**

# DATA SHEET



## PBSS3540F 40 V low V<sub>CEsat</sub> PNP transistor

Product specification Supersedes data of 2004 May 04 2004 Jun 11





Philips Semiconductors Product specification

## 40 V low V<sub>CEsat</sub> PNP transistor

#### **PBSS3540F**

#### **FEATURES**

- · Low collector-emitter saturation voltage
- · High current capability
- Improved thermal behaviour due to flat leads
- Enhanced performance over SOT23 general purpose transistors.

#### **APPLICATIONS**

- · General purpose switching and muting
- Low frequency driver circuits
- · Audio frequency general purpose applications
- Battery driven equipment (mobile phones, video cameras, hand-held devices).

#### **DESCRIPTION**

PNP low  $V_{\text{CEsat}}$  transistor in a SC-89 (SOT490) plastic package.

NPN complement: PBSS2540F.

#### **MARKING**


TYPE NUMBER	MARKING CODE
PBSS3540F	2D

#### **QUICK REFERENCE DATA**

SYMBOL	SYMBOL PARAMETER		UNIT
$V_{CEO}$	collector-emitter voltage	-40	<b>V</b>
I <sub>CM</sub>	peak collector current	<b>-1</b>	Α
R <sub>CEsat</sub>	equivalent on-resistance	<700	mΩ

#### **PINNING**

PIN	DESCRIPTION
1	base
2	emitter
3	collector



#### **ORDERING INFORMATION**

TYPE NUMBER		PACKAGE	
TIPE NOWIBER	NAME	DESCRIPTION	VERSION
PBSS3540F	_	plastic surface mounted package; 3 leads	SOT490

2004 Jun 11 2

Philips Semiconductors Product specification

## 40 V low $V_{CEsat}$ PNP transistor

PBSS3540F

#### **LIMITING VALUES**

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V <sub>CBO</sub>	collector-base voltage	open emitter	_	-40	V
V <sub>CEO</sub> collector-emitter voltage		open base	_	-40	V
V <sub>EBO</sub> emitter-base voltage		open collector	_	-6	V
I <sub>C</sub> collector current (DC)			_	-500	mA
I <sub>CM</sub>	peak collector current		_	-1	Α
I <sub>BM</sub>	peak base current		_	-100	mA
P <sub>tot</sub> total power dissipation		T <sub>amb</sub> ≤ 25 °C	_	250	mW
T <sub>stg</sub>	storage temperature		-65	+150	°C
Tj	junction temperature		_	150	°C
T <sub>amb</sub> operating ambient temperature			-65	+150	°C

#### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R <sub>th(j-a)</sub>	thermal resistance from junction to ambient	in free air	500	K/W

#### **CHARACTERISTICS**

 $T_{amb}$  = 25 °C unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
I <sub>CBO</sub>	collector-base cut-off current	$V_{CB} = -40 \text{ V}; I_E = 0 \text{ A}$	_	_	-100	nA
		$V_{CB} = -40 \text{ V}; I_E = 0 \text{ A}; T_j = 150 ^{\circ}\text{C}$	_	_	-50	μΑ
I <sub>BEO</sub>	emitter-base cut-off current	$V_{EB} = -5 \text{ V}; I_C = 0 \text{ A}$	_	_	-100	nA
h <sub>FE</sub>	DC current gain	V <sub>CE</sub> = −2 V				
		$I_{C} = -10 \text{ mA}$	200	-	_	
		$I_{C} = -100 \text{ mA}$ ; note 1	150	-	_	
		$I_{C} = -500 \text{ mA}$ ; note 1	40	_	_	
V <sub>CEsat</sub>	collector-emitter saturation voltage	$I_C = -10 \text{ mA}; I_B = -0.5 \text{ mA}$	_	_	-50	mV
		$I_C = -100 \text{ mA}; I_B = -5 \text{ mA}$	_	-	-130	mV
		$I_C = -200 \text{ mA}; I_B = -10 \text{ mA}$	_	_	-200	mV
		$I_C = -500 \text{ mA}$ ; $I_B = -50 \text{ mA}$ ; note 1	_	-	-350	mV
R <sub>CEsat</sub>	equivalent on-resistance	$I_C = -500 \text{ mA}$ ; $I_B = -50 \text{ mA}$ ; note 1	_	440	<700	mΩ
$V_{BEsat}$	base-emitter saturation voltage	$I_C = -500 \text{ mA}; I_B = -50 \text{ mA}; \text{ note 1}$	_	_	-1.2	V
V <sub>BEon</sub>	base-emitter turn-on voltage	$V_{CE} = -2 \text{ V}; I_{C} = -100 \text{ mA}; \text{ note 1}$	_	_	-1.1	V
C <sub>c</sub>	collector capacitance	$V_{CB} = -10 \text{ V}; I_E = I_e = 0 \text{ A};$ f = 1 MHz	_	_	10	pF
f⊤	transition frequency	$I_C = -100 \text{ mA}; V_{CE} = -5 \text{ V};$ f = 100 MHz	100	300	_	MHz

#### Note

1. Pulse test:  $t_p \le 300~\mu s;~\delta \le 0.02.$ 

2004 Jun 11 3

Philips Semiconductors Product specification


## 40 V low $V_{\text{CEsat}}$ PNP transistor

PBSS3540F

#### **PACKAGE OUTLINE**

#### Plastic surface mounted package; 3 leads

**SOT490** 



VERSION IEC JEDEC EIAJ PROJECTION	OUTLINE		REFER	ENCES	EUROPEAN	ISSUE DATE
	VERSION	IEC	JEDEC	EIAJ	PROJECTION	ISSUE DATE
	SOT490			SC-89		98-10-23

2004 Jun 11 4

0.6

Philips Semiconductors Product specification

## 40 V low V<sub>CEsat</sub> PNP transistor

PBSS3540F

#### **DATA SHEET STATUS**

LEVEL	DATA SHEET STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)(3)</sup>	DEFINITION
I	Objective data	Development	This data sheet contains data from the objective specification for product development. Philips Semiconductors reserves the right to change the specification in any manner without notice.
II	Preliminary data	Qualification	This data sheet contains data from the preliminary specification. Supplementary data will be published at a later date. Philips Semiconductors reserves the right to change the specification without notice, in order to improve the design and supply the best possible product.
III	Product data	Production	This data sheet contains data from the product specification. Philips Semiconductors reserves the right to make changes at any time in order to improve the design, manufacturing and supply. Relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN).

#### **Notes**

- 1. Please consult the most recently issued data sheet before initiating or completing a design.
- 2. The product status of the device(s) described in this data sheet may have changed since this data sheet was published. The latest information is available on the Internet at URL http://www.semiconductors.philips.com.
- 3. For data sheets describing multiple type numbers, the highest-level product status determines the data sheet status.

#### **DEFINITIONS**

**Short-form specification** — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 60134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

#### **DISCLAIMERS**

Life support applications — These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes in the products - including circuits, standard cells, and/or software - described or contained herein in order to improve design and/or performance. When the product is in full production (status 'Production'), relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN). Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

2004 Jun 11 5

## Philips Semiconductors – a worldwide company

#### **Contact information**

For additional information please visit http://www.semiconductors.philips.com. Fax: +31 40 27 24825 For sales offices addresses send e-mail to: sales.addresses@www.semiconductors.philips.com.

© Koninklijke Philips Electronics N.V. 2004

SCA76

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

R75/03/pp6

Date of release: 2004 Jun 11

Document order number: 9397 750 13349

Let's make things better.





