

Precision Electronics Diagonal Cutters, with ground screw joint

DIN ISO 9654

79 52 125



79 62 125








- the assortment for highest standard of performance and results
- precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- precisely ground, sharp cutting edges with very small bevel for exact cutting on delicate components; also without bevel for flush cutting
- cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- joint with screw: precise, zero backlash operation of pliers
- precisely finished joint surfaces for smooth, low friction movement along the complete opening range
- low-friction double spring for gentle and even opening
- non-reflective finish
- low weight
- ergonomically shaped, two-colour dual component handles; blue/grey
- high quality ball bearing steel, forged

Model: 79 52 125

- pointed head, with very small bevel
- with lead catcher - no uncontrolled loss of cut wire ends

Model: 79 62 125

- pointed head, without bevel
- with lead catcher - no uncontrolled loss of cut wire ends

Article- No.	EAN 4003773-	Head	Handles	Style Symbols				B mm	A mm	D mm	Length mm	g
					Ø mm	Ø mm	Ø mm					
79 52 125	065135	polished	with two- colour dual component handles	5 	1,30	0,70	0,40	11,0	11,0	6,5	125	50
79 62 125	065142	polished	with two- colour dual component handles	6 	1,00	0,55	-	11,0	11,0	6,5	125	50

technical change and errors excepted