



Part Number : 2262061063

Product Description : Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Black

Series Number : 226206

Status : Active

Product Category : Power and Signal Cable Assemblies

---

## Documents & Resources


### Drawings

Drawing 2262061063\_sd.pdf

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2024)4144-DC (27 June 2024)                                       |
| EU RoHS            | Compliant per EU 2015/863   |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

## General

|                        |   |
|------------------------|---|
| Status                 | Active  |
| Category               | Power and Signal Cable Assemblies   |
| Series                 | 226206  |
| Description            | Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Black |
| Application            | Power, Wire-to-Board, Wire-to-Wire  |
| Assembly Configuration | Dual Ended Connectors   |
| Connector to Connector | Micro-Fit 3.0 Both Ends   |
| Product Family         | Micro-Fit Connector System  |
| Product Name           | Micro-Fit 3.0   |
| Type                   | Discrete Wire Assembly  |
| UPC                    | 198282218845  |

## Electrical

|                               |            |
|-------------------------------|------------|
| Current - Maximum per Contact | 8.5A       |
| Voltage - Maximum             | 300V AC/DC |

## Physical

|                                |                 |
|--------------------------------|-----------------|
| Cable Length                   | 300.00mm        |
| Circuits (Loaded)              | 6               |
| Circuits (maximum)             | 6               |
| Color - Resin                  | Black           |
| Gender                         | Female-Female   |
| Lock to Mating Part            | Yes             |
| Material - Metal               | Phosphor Bronze |
| Material - Plating Mating      | Tin             |
| Material - Plating Termination | Tin             |
| Material - Resin               | Polyester       |
| Net Weight                     | 21.168/g        |
| Number of Rows                 | 1               |
| Overmolded                     | No              |
| Packaging Type                 | Bag             |

|                             |                        |
|-----------------------------|------------------------|
| Pitch - Mating Interface    | 3.00mm                 |
| Plating min - Mating        | 1.016µm                |
| Plating min - Termination   | 1.016µm                |
| Single Ended                | No                     |
| Termination Interface Style | Crimp or Compression   |
| Wire/Cable Type             | Discrete Wire, UL 1061 |
| Wire Insulation Diameter    | 1.85mm max.            |
| Wire Size (AWG)             | 18                     |

---

## Mates With / Use With

### Mates with Part(s)

| Description                            | Part Number   |
|--|---------------|
| Micro-Fit 3.0 Single Row Plug Housings | <u>43640</u>  |
| Micro-Fit TPA Single Row Plug Housings | <u>200875</u> |
| Micro-Fit 3.0 Single Row Headers       | <u>43650</u>  |