



Features:

- Protections:Short circuit/Over load/Over voltage
- Cooling by free air convection
- LED indicator for power on
- 100% full load burn-in test
- All using 105°C long life electrolytic capacitors
- Withstand 300VAC surge input for 5 second
- High operating temperature up to 70°C
- · Withstand 5G vibration test
- High efficiency, long life and high reliability
- 3 years warranty


SPECIFICATION



MODEL		RS-150-3.3	RS-150-5	RS-150-12	RS-150-15	RS-150-24	RS-150-48	
ОИТРИТ	DC VOLTAGE	3.3V	5V	12V	15V	24V	48V	
	RATED CURRENT	30A	26A	12.5A	10A	6.5A	3.3A	
	CURRENT RANGE	0~30A	0 ~ 26A	0 ~ 12.5A	0 ~ 10A	0 ~ 6.5A	0 ~ 3.3A	
	RATED POWER	99W	130W	150W	150W	156W	158.4W	
	RIPPLE & NOISE (max.) Note.2	80mVp-p	80mVp-p	120mVp-p	120mVp-p	120mVp-p	200mVp-p	
	VOLTAGE ADJ. RANGE	3.2V ~ 3.5V	4.75 ~ 5.5V	11.4 ~ 13.2V	14.25 ~ 16.5V	22.8 ~ 26.4V	45.6 ~ 52.8V	
	VOLTAGE TOLERANCE Note.3	±3.0%	±2.0%	±1.0%	±1.0%	±1.0%	±1.0%	
	LINE REGULATION Note.4	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	LOAD REGULATION Note.5	±2.0%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	
	SETUP, RISE, HOLD TIME	800ms, 20ms, 20ms	230VAC 1200ms	s, 30ms, 10ms/115VAC	at full load			
INPUT	VOLTAGE RANGE	88 ~ 132VAC / 176 ~ 264VAC selected by switch 248 ~ 373VDC(Withstand 300VAC surge for 5sec. Without damage)						
	FREQUENCY RANGE	47 ~ 63Hz						
	EFFICIENCY(Typ.)	74%	78%	83%	84%	86%	87%	
	AC CURRENT	3A/115VAC 2A/230VAC						
	INRUSH CURRENT(max.)	COLD START 50A/230VAC						
	LEAKAGE CURRENT	<2mA/240VAC						
PROTECTION		110 ~ 150% rated output power						
	OVER LOAD	Protection type: Hiccup mode, recovers automatically after fault condition is removed						
	OVEDVOLTAGE	3.8 ~ 4.45V	5.75 ~ 6.75V	13.8 ~ 16.2V	17.25 ~ 20.25V	27.6 ~ 32.4V	55.2 ~ 64.8V	
	OVER VOLTAGE	Protection type: Hiccup mode, recovers automatically after fault condition is removed						
ENVIRONMENT	WORKING TEMP.	-25 ~ +70°C (Refer to output load derating curve)						
	WORKING HUMIDITY	20 ~ 90% RH non-condensing						
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH						
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)						
	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, period for 60min. each along X, Y, Z axes						
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1 Approved						
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC						
SAFETY &	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms/500VDC						
EMC	EMI CONDUCTION & RADIATION	Compliance to EN55022 (CISPR22) Class B						
(Note 6)	HARMONIC CURRENT	Compliance to EN61000-3-2,-3						
	EMS IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11; ENV50204, EN61000-6-2 (EN50082-2) heavy industry level, criteria A						
	MTBF	244KHrs min. MIL-HDBK-217F (25°C)						
OTHERS	DIMENSION	199*98*38mm (L*W*H)						
	PACKING	0.7Kg; 20pcs/15Kg/0.72CUFT						
NOTE	Ripple & noise are measure Tolerance : includes set up Line regulation is measured Load regulation is measure	specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. easured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. set up tolerance, line regulation and load regulation. asured from low line to high line at rated load. easured from 0% to 100% rated load.						


- 6. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets
- 7. Length of set up time is measured at cold first start. Turning ON/OFF the power supply very quickly may lead to increase of the set up time.






Terminal Pin. No Assignment

Pin No.	Assignment	Pin No.	Assignment
1	AC/L	4,5	DC OUTPUT -V
2	AC/N	6,7	DC OUTPUT +V
3	FG ±		





■ Static Characteristics

