

97 Crimping Plier for Western Plugs



97 51 12




4-poles 6-poles 8-poles

- ▶ professional tool for cutting and stripping unshielded ribbon telephone cables
- ▶ for crimping 4-, 6- and 8-pole Western plugs type RJ 10 (7.65 mm width), type RJ 11/12 (9.65 mm width) and type RJ 45 (11.68 mm width)
- ▶ exact crimping process due to parallel crimping
- ▶ repetitive, high crimping quality due to integral lock (self-releasing mechanism)

- ▶ optimum transmission of force due to lever action for fatigue-reduced operation
- ▶ with length cutter and dismantling knife for ribbon cables 6 and 12 mm length
- ▶ head burnished, with two-colour dual component handles




Crimping Plier with cutting and dismantling device

Article-No.	EAN-Code	Range of Application	Capacity	Length	
				mm	g
97 51 12	4003773-043188	Western plugs 	RJ 10, (4-poles) 7.65 mm RJ 11/12 (6-poles) 9.65 mm RJ 45 (8-poles) 11.68 mm	200	530
97 59 06	029700	4 spare blades for 97 51 04 / 10 / 12			

97 Four-Mandrel Crimping Pliers for turned contacts



97 52 64



97 52 65



- ▶ for crimping turned contacts
- ▶ for solder-free electrical connections
- ▶ four-mandrel crimping for exact crimping performance
- ▶ mandrel gauge to check the basic setting
- ▶ locator for positioning the contacts
- ▶ repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- ▶ these tools have been set precisely (calibrated) in the factory
- ▶ optimum transmission of force due to lever action for fatigue-reduced operation
- ▶ high operation comfort thanks to handy shape
- ▶ all stressed parts are made of special steel, oil-hardened and tempered

Model 97 52 63:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ nickel plated head, two-colour dual component handles

Model 97 52 64:







- ▶ pressure adjustment depending on the conductor's diameter by means of adjusting wheel in 4 different positions
- ▶ nickel plated head, two-colour dual component handles

Model 97 52 65:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ nickel plated head, plastic handles



Four-mandrel squeezing for exact crimping performance

Article-No.	EAN-Code	Range of Application	Capacity	Length		
			mm ²	AWG	mm	g
97 52 63	4003773-050148	 turned contacts 	0.08 - 2.5	28 - 13	180	370
97 52 64	041481	 turned contacts 	0.08 - 2.5	28 - 13	180	415
97 52 65	045236	 turned contacts (Harting) 	0.14 - 6.0	26 - 10	230	680