

☒ Region ▶ EMEA ☒ Part Number ▶ HV9150-C0 ☒ Product Family ▶ Hyper-V™ In-Line Cable Ties

[Hyper-V™ Cable Tie Mounts](#)



- Fixed and flexible two-wedge locking design provides a low threading force
- Teeth on both sides of cable tie body provide additional locking strength and improved flexibility to conform to irregular bundle shapes such as securing cables to cable tray systems
- Releasable head position for temporary bundling of cables prior to final locking; no need to replace ties when adding cables/wires to the bundle
- Teeth on full length of body support a wide range of bundle diameters
- Bending serrations on the tip of the tie allows the tip to be easily formed into an arc, enabling installer to "fish" the tie around the bundle in a confined space
- Threading hole in the tip of the tie allows an installer to hook the tip with a simple device to pull the tie through spaces with limited access
- In-Line tie design for parallel-entry of the tie into head resulting in a lower profile on cable bundles
- Complementary mounts available

Part Number:	HV9150-C0
Product Family:	Hyper-V™ In-Line Cable Ties
Product Line:	Hyper-V In-Line Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Hyper-V™ In-Line Cable Tie, 20.7", Light-Heavy cross section
Product Type:	Cable Ties
Material:	Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	No
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	No
Length (In.):	20.7
Length (mm):	525
Width (In.):	.350
Width (mm):	8.9
CE Compliant:	Yes
Cross Section:	Light-Heavy
Head Height (In.):	.318
Head Height (mm):	8.0
Head Width (In.):	.571
Head Width (mm):	14.5
Locking Style:	Locking
Material Flammability Rating:	UL94-HB
Max. Bundle Diameter (In.):	5.90
Max. Bundle Diameter (mm):	150
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	160
Min. Loop Tensile Strength (N):	710
Thickness (In.):	.076