


# SOT23 NPN SILICON PLANAR MEDIUM POWER HIGH PERFORMANCE TRANSISTOR

## FMMT495

ISSUE 3 - NOVEMBER 1995

PARTMARKING DETAIL - 495



### ABSOLUTE MAXIMUM RATINGS.

| PARAMETER                                  | SYMBOL         | VALUE       | UNIT        |
|--|----------------|-------------|-------------|
| Collector-Base Voltage                     | $V_{CBO}$      | 170         | V           |
| Collector-Emitter Voltage                  | $V_{CEO}$      | 150         | V           |
| Emitter-Base Voltage                       | $V_{EBO}$      | 5           | V           |
| Continuous Collector Current               | $I_C$          | 1           | A           |
| Peak Pulse Current                         | $I_{CM}$       | 2           | A           |
| Base Current                               | $I_B$          | 200         | mA          |
| Power Dissipation at $T_{amb}=25^{\circ}C$ | $P_{tot}$      | 500         | mW          |
| Operating and Storage Temperature Range    | $T_j; T_{stg}$ | -55 to +150 | $^{\circ}C$ |

### ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ ).

| PARAMETER                             | SYMBOL         | MIN. | MAX. | UNIT | CONDITIONS.   |
|---------------------------------------|----------------|------|------|------|---|
| Breakdown Voltages                    | $V_{(BR)CBO}$  | 170  |      | V    | $I_C=100\mu A$  |
|                                       | $V_{CEO(sus)}$ | 150  |      | V    | $I_C=10mA^*$  |
|                                       | $V_{(BR)EBO}$  | 5    |      | V    | $I_E=100\mu A$  |
| Collector Cut-Off Currents            | $I_{CBO}$      |      | 100  | nA   | $V_{CB}=150V$   |
|                                       | $I_{CES}$      |      | 100  | nA   | $V_{CE}=150V$   |
| Emitter Cut-Off Current               | $I_{EBO}$      |      | 100  | nA   | $V_{EB}=4V$   |
| Collector-Emitter Saturation Voltage  | $V_{CE(sat)}$  |      | 0.2  | V    | $I_C=250mA, I_B=25mA^*$<br>$I_C=500mA, I_B=50mA^*$  |
|                                       |                |      | 0.3  | V    |   |
| Base-Emitter Saturation Voltage       | $V_{BE(sat)}$  |      | 1.0  | V    | $I_C=500mA, I_B=50mA^*$   |
| Base-Emitter Turn On Voltage          | $V_{BE(on)}$   |      | 1.0  | V    | $I_C=500mA, V_{CE}=10V^*$   |
| Static Forward Current Transfer Ratio | $h_{FE}$       | 100  | 300  |      | $I_C=1mA, V_{CE}=10V$<br>$I_C=250mA, V_{CE}=10V^*$<br>$I_C=500mA, V_{CE}=10V^*$<br>$I_C=1A, V_{CE}=10V^*$ |
|                                       |                | 100  |      |      |   |
|                                       |                | 50   |      |      |   |
|                                       |                | 10   |      |      |   |
| Transition Frequency                  | $f_T$          | 100  |      | MHz  | $I_C=50mA, V_{CE}=10V$<br>$f=100MHz$  |
| Collector-Base Breakdown Voltage      | $C_{obo}$      |      | 10   | pF   | $V_{CB}=10V, f=1MHz$  |

\*Measured under pulsed conditions. Pulse width=300 $\mu s$ . Duty cycle  $\leq 2\%$

# FMMT495

## TYPICAL CHARACTERISTICS

