National Semiconductor

February 1996

DS3695A/DS3695AT/DS3696A Multipoint RS485/RS422 Transceivers

General Description

The DS3695A and DS3696A are high speed differential TRI-STATE® bus/line transceivers designed to meet the requirements of EIA standard RS485 with extended common mode range (+12V to –7V), for multipoint data transmission. In addition they are compatible with requirements of RS-422.

The driver and receiver outputs feature TRI-STATE capability. The driver outputs remain in TRI-STATE over the entire common mode range of +12V to –7V. Bus faults that cause excessive power dissipation within the device trigger a thermal shutdown circuit, which forces the driver outputs into the high impedance state. The DS3696A provides an output pin (TS) which reports the thermal shutdown of the device. TS is an "open collector" pin with an internal 10 kΩ pull-up resistor. This allows the TS outputs of several devices to be wire OR-ed.

Both AC and DC specifications are guaranteed over the 0˚C to 70˚C temperature and 4.75V to 5.25V supply voltage range.

Features

- Meets EIA standard RS485 for multipoint bus transmission and is compatible with RS-422
- 10 ns driver propagation delays (typical)
- Single +5V supply
- –7V to +12V bus common mode range permits ±7V ground difference between devices on the bus
- Thermal shutdown protection
- High impedance to bus with driver in TRI-STATE or with power off, over the entire common mode range allows the unused devices on the bus to be powered down
- Combined impedance of a driver output and receiver input is less than one RS485 unit load, allowing up to 32 transceivers on the bus
- 70 mV typical receiver hysteresis
- Available in SOIC packaging

Connection and Logic Diagram

Molded Package, Small Outline (M)



00527201

Top View



00527202

$\overline{TS}$ was $\overline{LF}$ (Line Fault) on previous datasheets, $\overline{TS}$ goes low upon thermal shutdown.

Top View
Order Number DS3695AM, DS3695ATM or DS3696AM
See NS Package Number M08A

TRI-STATE® is a registered trademark of National Semiconductor Corporation.

Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Supply Voltage, V_{CC}	7V
Control Input Voltages	7V
Driver Input Voltage	7V
Driver Output Voltages	+15V/−10V
Receiver Input Voltages	+15V/−10V
Receiver Output Voltage	5.5V
Continuous Power Dissipation @ 25˚C	
M Package	630 mW (Note 4)
Storage Temp. Range	−65˚C to +150˚C
Lead Temp. (Soldering 4 seconds)	260˚C

Recommended Operating Conditions

	Min	Max	Units
Supply Voltage, V_{CC}	4.75	5.25	V
Bus Voltage	−7	+12	V
Operating Free Air Temp. (T_A)			
Commercial (DS3695AM)	0	+70	˚C
Industrial (DS3695ATM)	−40	+85	˚C
Commercial (DS3696AM)	0	+70	˚C

Electrical Characteristics (Notes 2, 3)

$0˚C \le T_A \le 70˚C$, $4.75V < V_{CC} < 5.25V$ unless otherwise specified

Symbol	Parameter		Conditions		Min	Typ	Max	Units
V_{OD1}	Differential Driver Output Voltage (Unloaded)		$I_O = 0$				5	V
V_{OD2}	Differential Driver Output Voltage (with Load)			R = 50Ω; (RS-422) (Note 5)	2			V
				R = 27Ω; (RS-485)	1.5			V
ΔV_{OD}	Change in Magnitude of Driver Differential Output Voltage For Complementary Output States						0.2	V
V_{OC}	Driver Common Mode Output Voltage			R = 27Ω			3.0	V
$\Delta\lvert V_{OC}\rvert$	Change in Magnitude of Driver Common Mode Output Voltage For Complementary Output States						0.2	V
V_{IH}	Input High Voltage	DI, DE, $\overline{RE}$, R$\overline{E}$ /DE			2			V
V_{IL}	Input Low Voltage						0.8	V
V_{CL}	Input Clamp Voltage			I_{IN} = −18 mA			−1.5	V
I_{IL}	Input Low Current			V_{IL} = 0.4V			−200	µA
I_{IH}	Input High Current			V_{IH} = 2.4V			20	µA
I_{IN}	Input Current	DO/RI, $\overline{DO}$ /$\overline{RI}$	V_{CC} = 0V or 5.25V	V_{IN} = 12V			+1.0	mA
		RI, $\overline{RI}$	DE or R$\overline{E}$ /DE = 0V	V_{IN} = −7V			−0.8	mA
V_{TH}	Differential Input Threshold Voltage for Receiver		$-7V \le V_{CM} \le +12V$		−0.2		+0.2	V
ΔV_{TH}	Receiver Input Hysteresis		V_{CM} = 0V			70		mV
V_{OH}	Receiver Output High Voltage		I_{OH} = −400 µA		2.4			V
V_{OL}	Output Low Voltage	RO	I_{OL} = 16 mA (Note 5)				0.5	V
		$\overline{TS}$	I_{OL} = 8 mA				0.45	V
I_{OZR}	OFF-State (High Impedance) Output Current at Receiver		V_{CC} = Max $0.4V \le V_O \le 2.4V$				±20	µA
R_{IN}	Receiver Input Resistance		$-7V \le V_{CM} \le +12V$		12			kΩ
I_{CC}	Supply Current		No Load	Driver Outputs Enabled		42	60	mA
			(Note 5)	Driver Outputs Disabled		27	40	mA
I_{OSD}	Driver Short-Circuit Output Current		V_O = −7V (Note 5)				−250	mA
			V_O = +12V (Note 5)				+250	mA
I_{OSR}	Receiver Short-Circuit Output Current		V_O = 0V		−15		−85	mA

Note 1: "Absolute maximum ratings" are those beyond which the safety of the device cannot be guaranteed. They are not meant to imply that the device should be operated at these limits. The tables of "Electrical Characteristics" provide conditions for actual device operation.

Note 2: All currents into device pins are positive; all currents out of device pins are negative. All voltages are referenced to device ground unless otherwise specified.

Note 3: All typicals are given for V_{CC} = 5V and T_A = 25˚C.

Note 4: Derate linearly at 6.5 mW/˚C to 337 mW at 70˚C.

Note 5: All limits for which Note 5 is applied must be derated by 10% for DS3695AT. Other parameters remain the same for this extended temperature range device (−40˚C ≤ T_A ≤ +85˚C).

Switching Characteristics

0˚C ≤ T_A ≤ 70˚C, 4.75V < V_{CC} < 5.25V unless otherwise specified (Note 3)

Receiver Switching Characteristics

(*Figures 1, 2* and *Figure 3*)

Symbol	Conditions	Min	Typ	Max	Units
t_{PLH}	C_L = 15 pF	15	28	42	ns
t_{PHL}	S1 and S2	15	28	42	ns
$\|t_{PLH}-t_{PHL}\|$	Closed	0	3		ns
t_{PLZ}	C_L = 15 pF, S2 Open	5	29	35	ns
t_{PHZ}	C_L = 15 pF, S1 Open	5	12	16	ns
t_{PZL}	C_L = 15 pF, S2 Open	7	15	28	ns
t_{PZH}	C_L = 15 pF, S1 Open	7	15	20	ns

Driver Switching Characteristics

Symbol	Conditions	Min	Typ	Max	Units
SINGLE ENDED CHARACTERISTICS (*Figures 4, 5* and *Figure 7*)					
t_{PLH}	R_{LDIFF} = 60Ω	9	15	22	ns
t_{PHL}	C_{L1} = C_{L2} = 100 pF	9	15	22	ns
$t_{SKEW}\|t_{PLH}-t_{PHL}\|$		0	2	8	ns
t_{PLZ}	C_L = 15 pF, S2 Open	7	15	30	ns
t_{PHZ}	C_L = 15 pF, S1 Open	7	15	30	ns
t_{PZL}	C_L = 100 pF, S2 Open	30	35	50	ns
t_{PZH}	C_L = 100 pF, S1 Open	30	35	50	ns
DIFFERENTIAL SWITCHING CHARACTERISTICS (*Figure 7*)					
t_r, t_f	R_{LDIFF} = 60Ω C_{L1} = C_{L2} = 100 pF	6	10	18	ns

AC Test Circuits and Switching Waveforms



FIGURE 1. Receiver Propagation Delay Test Circuit

AC Test Circuits and Switching Waveforms (Continued)



Differential input voltage may be realized by grounding $\overline{RI}$ and pulsing RI between +2.5V and −2.5V

FIGURE 2. Receiver Input-to-Output Propagation Delay Timing



FIGURE 3. Receiver Enable/Disable Propagation Delay Timing



Unless otherwise specified the switches are closed.



FIGURE 4. Driver Propagation Delay Test Circuits

AC Test Circuits and Switching Waveforms (Continued)



t_{PLH} and t_{PHL} are measured to the respective 50% points. t_{SKEW} is the difference between propagation delays of the complementary outputs.

FIGURE 5. Driver Input-to-Output Propagation Delay Timing (Single-Ended)



FIGURE 6. Driver Enable/Disable Propagation Delay Timing



FIGURE 7. Driver Differential Transition Timing

Function Tables

DS3695A/DS3696A Transmitting

Inputs			Line	Outputs		
$\overline{RE}$	DE	DI	Condition	$\overline{DO}$	DO	$\overline{TS}$ * (DS3696A Only)
X	1	1	No Fault	0	1	H
X	1	0	No Fault	1	0	H
X	0	X	X	Z	Z	H
X	1	X	Fault	Z	Z	L

DS3695A/DS3696A Receiving

Inputs			Output	
$\overline{RE}$	DE	RI–$\overline{RI}$	RO	$\overline{TS}$ * (DS3696A Only)
0	0	≥+0.2V	1	H
0	0	≤–0.2V	0	H
0	0	Inputs Open**	1	H
1	0	X	Z	H

X — Don't care condition
Z — High impedance state
Fault — Improper line conditions causing excessive power dissipation in the driver, such as shorts or bus contention situations
* $\overline{TS}$ is an "open collector" output with an on-chip 10 kΩ pull-up resistor.
** **This is a fail safe condition**

Typical Application



00527218

Repeater control logic not shown. See AN-702.

Physical Dimensions inches (millimeters) unless otherwise noted



Molded SOIC Package (M)
Order Number DS3695AM, DS3695ATM or DS3696AM
NS Package Number M08A

National Semiconductor
Americas Customer
Support Center
Email: new.feedback@nsc.com
Tel: 1-800-272-9959

www.national.com

National Semiconductor
Europe Customer Support Center
Fax: +49 (0) 180-530 85 86
Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 69 9508 6208
English Tel: +44 (0) 870 24 0 2171
Français Tel: +33 (0) 1 41 91 8790

National Semiconductor
Asia Pacific Customer
Support Center
Email: ap.support@nsc.com

National Semiconductor
Japan Customer Support Center
Fax: 81-3-5639-7507
Email: jpn.feedback@nsc.com
Tel: 81-3-5639-7560