
2SK1056, 2SK1057, 2SK1058

Silicon N-Channel MOS FET

HITACHI

November 1996

Application


Low frequency power amplifier

Complementary pair with 2SJ160, 2SJ161 and 2SJ162

Features

- Good frequency characteristic
- High speed switching
- Wide area of safe operation
- Enhancement-mode
- Good complementary characteristics
- Equipped with gate protection diodes
- Suitable for audio power amplifier

Outline



2SK1056, 2SK1057, 2SK1058

Absolute Maximum Ratings (Ta = 25°C)

Item	Symbol	Ratings	Unit
Drain to source voltage	2SK1056	V _{DSX}	120
	2SK1057		140
	2SK1058		160
Gate to source voltage	V _{GSS}	±15	V
Drain current	I _D	7	A
Body to drain diode reverse drain current	I _{DR}	7	A
Channel dissipation	Pch* ¹	100	W
Channel temperature	T _{Ch}	150	°C
Storage temperature	T _{Stg}	−55 to +150	°C


Notes 1. Value at T_c = 25°C

Electrical Characteristics (Ta = 25°C)

Item	Symbol	Min	Typ	Max	Unit	Test conditions
Drain to source breakdown voltage	2SK1056	V _{(BR)DSX}	120	—	—	V I _D = 10 mA, V _{GS} = −10 V
	2SK1057		140			
	2SK1058		160			
Gate to source breakdown voltage	V _{(BR)GSS}	±15	—	—	V I _G = ±100 μA, V _{DS} = 0	
Gate to source cutoff voltage	V _{GS(off)}	0.15	—	1.45	V I _D = 100 mA, V _{DS} = 10 V	
Drain to source saturation voltage	V _{DS(sat)}	—	—	12	V I _D = 7 A, V _{GD} = 0 * ¹	
Forward transfer admittance	y _{fs}	0.7	1.0	1.4	S I _D = 3 A, V _{DS} = 10 V * ¹	
Input capacitance	C _{iss}	—	600	—	pF V _{GS} = −5 V, V _{DS} = 10 V, f = 1 MHz	
Output capacitance	C _{oss}	—	350	—	pF	
Reverse transfer capacitance	C _{rss}	—	10	—	pF	
Turn-on time	t _{on}	—	180	—	ns V _{DD} = 20 V, I _D = 4 A,	
Turn-off time	t _{off}	—	60	—	ns	

Note 1. Pulse test

2SK1056, 2SK1057, 2SK1058



2SK1056, 2SK1057, 2SK1058

