

# LIFE NANO Wireless Laser Mobile Mouse

## M-300R



### Facts & Features

- Ergonomic laser mouse for right-handed users with secure 2.4 GHz wireless technology and a particularly small USB-receiver
- Nano USB-receiver which can remain in the laptop or be stored in the mouse when you're on the move
- Laser sensor for precise work. Simple toggle of the resolution (slow / fast) via an easily-accessible switch on the top of the mouse
- Wireless freedom with 2.4 GHz wireless technology offering up to 5 m range and interruption-free transmission
- Ideal for use on the move with an energy-saving On/Off switch
- Plug & Play for easy start up with no software installation

### Delivery volume

- 1 LIFE NANO Mouse
- 1 Nano-USB-receiver
- 1 printed manual with warranty declaration
- 1 batterie (AA)

### Approvals

- CE, FCC

### Operating system

- Microsoft Windows® XP, Vista

### System requirements

- USB interface

### Technical data

- Number of buttons:  
5 buttons
- Weight:  
approx. 80g (mouse)  
approx. 10g (receiver)  
approx. 190g (incl. packaging)
- Dimensions in mm:  
approx. 110 x 65 x 40 (mouse)  
approx. 122 x 250 x 84 (packaging)
- Storage temperature:  
-20°C to 60°C
- Operating temperature:  
0°C to 40°C
- Transmission range:  
approx. 5 m
- Resolution:  
800 dpi / 1600 dpi (laser)
- Frequency range:  
2.4 GHz
- Interface:  
USB
- Current consumption:  
typ. 30 mA (receiver)  
max. 15 mA (mouse)
- Packaging unit:  
10 mice per master carton  
48 master cartons per pallet

## Order description

<i>Order number</i>	<i>Housing colour</i>	<i>Interface</i>	<i>EAN-Code</i>
M-300R	black	USB	4025112067730

Cherry GmbH  
Cherrystraße  
91275 Auerbach/Opf.  
Germany

Phone: +49 9643 18-0  
Internet: [www.cherry.de](http://www.cherry.de)  
[www.cherrycorp.com](http://www.cherrycorp.com)

Sales: +49 1805 243779 (01805-Cherry)  
E-Mail: [sales@cherry.de](mailto:sales@cherry.de)  
Fax: +49 9643 18-1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 Cherry GmbH, Last update: 18.07.2008\_V02

