



Silent, mobile industrial Wet&Dry vacuum cleaners with superior suction power

ATTIX 30 represents a new possibility of achieving superior suction power in a compact and flexible solution. Silent, small and mobile, but with the same convincing suction performance as ATTIX 50. A perfect solution for craftsmen on the move. Available with Push&Clean or XtremeClean system.

The small size and big performance of the ATTIX 30, along with the wide range of available models, make it a perfect choice for people who move with their work from place to place.

Operating costs are minimized with the washable PET Fleece filter elements, and the low working noise level lets you work when others are nearby, without disturbing them. The excellent design offers you cable storage, accessories storage and a big tool deposit to keep all you need at hand. The basic wet and dry vacuum cleaners are designated as the -O1 models. Automatic On/Off models (designated as the -21 models) are the choice of people who use the machine with electric hand tools because starting or stopping the tool starts and stops the vacuum, as well. An accessory Airbox is available which performs the same function when using pneumatic tools. While dealing with fine dust the Push&Clean Filter cleaning system offers a comfortable and quick way to clean the filter. For even better performance the new generation XtremeClean automatic filter cleaning system will clean the filter without any interruptions. The Multifit system allows the use of the complete range of accessories.

PRODUCT FACTS

- Compact, ergonomic and powerful.
- Push&Clean filter cleaning system takes care of filter cleaning tasks in just a few seconds.
- Washable PET fleece filter for high efficiency and low maintenance costs.
- SilentPower. High performance that is seen, but not heard.
- 30 litre container volume and a Fleece filter bag for the ultimate in effective filtration.
- The 30
- 01PC comes complete with 3m x 32mm diam hose, floor nozzle, al ext tube and crevice nozzle.
- The 30
- 21PC comes with just a 27mm diam antistatic hose fitted with a power tool adapter.

Model	ATTIX 30-01	ATTIX 30-01	ATTIX 30-21 PC	ATTIX 30-21 PC
Ref. no	302003625	302003626	302003627	302003628
Description	ATTIX 30-01PC 230V	ATTIX 30-01PC 110V	ATTIX 30-21PC 230V	ATTIX 30-21PC 110V







PRODUCT FEATURES

AUTOMATIC ON/OFF-ELEC. TOOLS			■	■
SOFTSTART			■	■
CABLE STORAGE	■	■	■	■
GENUINE RUBBER MAINS CABLE	■	■	■	■
ANTI-STATIC SYSTEM			■	■
PUSH & CLEAN FILTER CLEANING	■	■	■	■
WASHABLE PET FLEECE FILTER	■	■	■	■
XTRMECLEAN AUTO FILTER CLEANING				
TUBE HOLDER	■	■	■	■
LOW WORKING SOUND LEVEL	■	■	■	■
MULTI-FIT ACCESSORY SYSTEM	■	■	■	■
STORAGE OF ACCESSORIES	■	■	■	■

INCL. ACCESSORIES

302000477 COMBINATION FLOOR NOZZLE	■	■		
6084 CREVICE TOOL PLASTIC 290M	■	■		
302000804 DISPOSAL BAG X 5 ATTIX 30				
302000529 EXTN TUBE ?36 2X500MM CR	■	■		
302000490 FILTER ELEMENT	■	■	■	■
302002842 FLAT FILTER SET 2PCS				
302001682 HOSE AS36MMX5M W/TOOL				
15325 SUCTION HOSE DN 27MM LT 3			■	■
46948 SUCTION HOSE DN 36MM LT 3	■	■		
302000535 TOOL SOCKET Ø27				

Technical specifications	ATTIX 30-01	ATTIX 30-01	ATTIX 30-21 PC	ATTIX 30-21 PC
APPROVAL	CE/GS	CE/GS	CE/GS	CE/GS
EL CABLE (M)	7,5	7,5	7,5	7,5
POWER PMAX (W)	1500	1150	1500	1150
POWER PIEC (W)	1200	1000	1200	1000
MAINS CONNECTION (V/~ /HZ/A)	230/1/50/16	110/1/50/16	230/1/50/16	110/1/50/32
AIR FLOW RATE (L/M)	3700	3200	3700	3200
VACUUM (MBAR/KPA)	250/25	230/23	250/25	230/23
WORKING SOUND LEVEL (DB-A)	59	59	59	59
CONTAINER VOLUME (L-MAX)	30	30	30	30
DIMENSIONS LXWXH (MM)	450x380x595	450x380x595	450x380x595	450x380x595
WEIGHT (KG)	10	10	10	10

Accessories		Ref. no	Min. required	ATTIX 30-01	ATTIX 30-21 PC
	Tube				
	CHROME CURVED HAND TUBE D N 36	302000528	1	■	■
	Hose Vacuum cleaners				
	HOSE AS36MMX5M W/TOOL ADAPTER	302001682	1	■	■
	Bag				
	FLEECE FILTER BAGS X 5 ATTIX 30	302004000	1	■	■
	Others				
	TOOL SOCKET Ø27	302000535	1	■	■
	Extension tubes				
	2 X 500MM EXTENSION TUBE ALUMINIUM	107400032	1	■	■
	Vacuum Accessory Sets				
	WORKSHOP SET	302000927	1	■	■
	ANIMAL CARE SET	6095	1	■	■
	HOSE SET SQ 36MM	63210	1	■	■
	AUTO SET 36MM SQ	63211	1	■	■
	KIT	63212	1	■	■
	HANDLE INDUSTRIAL SET 36M M SQ	63213	1	■	■
	INDUSTRIAL KIT EXTRA 36MM	63214	1	■	■
PIPE VAC KIT	63215	1	■	■	