



FXX^{*1)}S1GY^{*2)} e.g. F15S1G1

*1) xx No. of contacts 09, 15, 25 or 37
*2) y for performance classes 1, 2 or 3
(contact cycle for G1/G2/G3 = 500/200/50)

xx	A [mm]	B [mm]	C [mm]	*E [mm]
09	30.8	16.4	25	
15	39.1	24.7	33.3	∅1
25	53	38.5	47.04	
37	69.3	54.9	63.5	

RoHS compliant

*PCB hole patterns, ∅E on supplement AM0023

3	xx	Signal contact	S1 / Brass	G1/G2/G3
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +125°C)	white
No.	St.	Part	Type Description/Material Surface plating/Colour/Class	

Measurement without tolerance		SCALE	TITLE
ISO 2768-m		2:1	
NAME / DATE	Denzinger		
DRAWN	11-02-2003		
CHECKED	Flößmann		
	12-02-2003		

1	REV.	DATE	CH.-NO.	DWG.NO.	REPLACEMENT FOR:	PAGES
				FxxS1Gy	FxxS1Gy,0	1
						1

