



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	05/17/12	D.GRIFFIN



KIT CONTAINS ITEMS LISTED BELOW:

- (1) Lightweight Ergonomic Ratcheting Crimp Frame
- (5) Interchangeable Crimp Dies with the following Crimp Dimensions:
 - Die 1 = .256", .213", .068"
 - Die 2 = .028", .039", .047", .100", .128", .151"
 - Die 3 = .100", .128", .429"
 - Die 4 = .068", .213", .256", .324"
 - Die 5 = 1.5mm, 2.5mm, 6mm, 10mm
- (1) Assembly Screwdriver
- (1) Adjustable Coax Cable Stripper for LMR@/WBC100, 174, 195, 200, 240 and 316, HyperLink CA-200/CA-240, RG58, 59, 62 and 6 Cable (AT-STRIP-01)
- (1) Adjustable Coax Cable Stripper for LMR@/WBC400, HyperLink CA-400, RG8, 11, 213 and 214 Cable (AT-STRIP-02)
- (1) Cable Cutter
- (1) Carrying Case

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $> 12 [305] - 60 [1524] = +2 [51] / -0$ $> 60 [1524] - 120 [3048] = +4 [102] / -0$ $> 120 [3048] - 300 [7620] = +6 [152] / -0$ $> 300 [7620] = +5\% / -0\%$ ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 .XX = .02 .XXX = .005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D.PARHAM	05/17/2012				
	CHECKED BY ENG	05/17/2012	CATEGORY	COAXIAL		
	APPROVED BY ENG	05/17/2012	PRODUCT DESCRIPTION	10 PIECE CRIMP TOOL KIT		
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. HT-KIT-01	REV. A
	SCALE: 1:1		CAD FILE: HT-KIT-01.SLDRW		SHEET 1 OF 1	