



complete length when assembled app. 42 mm

width across flat 18

width across flat 19

width across flat 15

A (2:1)

contact face acc. to IEC 61076-2-101

assembly aid enclosed

panel thickness

Panel cut out (1:1)

min.2 - max.5

Ø16,3±0,2

14,3±0,2

- recommended torque of counter nut: 2Nm
- order contacts separately

cable Ø			wire gauge	part-no.
5,7 - 6,9mm	6,5 - 7,7mm	7,5 - 8,8mm		
sealing			AWG 26-22	09 67 000 5476
A	B	C	AWG 24-20	09 67 000 8476
			AWG 22-18	09 67 000 3476

	All Dimensions in mm Original Size DIN A4		Scale 1:1	Free size tol.		Ref.	
	All rights reserved Department EC PD - RO		Created by POPESCUD	Inspected by AVRAM	Standardisation HOFFMANN	Date 2017-07-06	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp			Title PFT Slim design female D-coded			Doc-Key / ECM-Nr. 100622621/UGD/001/E 500000121871	
			Type TB	Number 21038812425		Rev. E	Page 1/1