







REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
B		PROPOSAL	05/11/18	L.CHAN
C		PROPOSAL	05/11/18	L.CHAN



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)



RECOMMENDED PANEL CUTOUT

PART NUMBER: RJHSE-X38X-06

- GOLD PLATING**
- E = RJ45 FLAT CONTACT 6 μ INCH
 - G = RJ45 FLAT CONTACT 15 μ INCH
 - J = RJ45 FLAT CONTACT 30 μ INCH
 - 5 = RJ45 FLAT CONTACT 50 μ INCH
- REFER TO LED OPTIONS DRAWING FOR ORDERING CODES

- MATERIALS:**
 PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK
 CONTACTS: PHOSPHOR BRONZE
 PLATING: GOLD ON MATING SURFACES (SEE PART NO. FOR THICKNESS).
 50 μ" [1.27 MICRONS]
 MIN. NICKEL UNDERPLATE
 100 μ" [2.54 MICRONS]
 MIN. MATTE TIN ON CONTACT TAILS.
 SHIELD: COPPER ALLOY
 PLATING: NICKEL
- MECHANICAL:**
 MATING FORCE: 5.0 LBS MAX.
 MATING CYCLES: 200
- ELECTRICAL:**
 CONTACT RESISTANCE: 20 MILLIOHMS MAXIMUM
 INSULATION RESISTANCE: 500 MEGOHMS MINIMUM
 CURRENT RATING: 1.5 AMPS
 VOLTAGE RATING: 125 VOLTS AC
- ENVIRONMENTAL:**
 STORAGE TEMPERATURE: -20°C to 85°C
 STORAGE LIFE: 1 YEAR
 PACKAGING METHOD: TRAY PACKAGING
- UL FILE NUMBER:** E135615

DRAWN PAULW	DATE 05/11/18	Amphenol Canada Corp.			
DESIGNED					
CHECKED CHIGOW	DATE 05/11/18	TITLE 6 PORT HIGH SPEED MODULAR JACK, 8 POSITIONS, 8 CONTACTS, WITH GOLD PLATING OPTION, WITH LEDS OPTION, WITH SHIELD - RoHS COMPLIANT			
I. E. APPRD.					
Q. A. APPRD.		DWG. DRAWING NO.		REV.	
DWG. APPRD.		P-RJHSE-X38X-06		C	
ENG. REL. NO.		SCALE	WT.	SURF.	
REF.		SHEET 1 OF 1			
DIMENSIONS ARE IN INCHES (mm)		CODE ID. NO. 03554			

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.