









PRODUCT NUMBER	DIM A	DIM B	NOTES
84620-XYLF	10.00	11.88	TOOLED

NOTES:

- SEE APPLICATION SPECIFICATION GS-20-010 FOR INFORMATION ON AVAILABLE TOOLING, CIRCUIT BOARD DESIGN CONSIDERATIONS, REPAIR PROCEDURES AND PRODUCT OFFERINGS.
- UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5, 1994.
- MATERIAL : BODY : THERMOPLASTIC UL94-V0. 
: CONTACT : COPPER ALLOY.
- FOR PLATING PERFORMANCE REFER DRAWING # 10159408. 
- THE PRODUCTS PARTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004. 
- ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260° FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION
- 84620-XYLF.

'X' REFER DRAWING # 10159408 



spec ref		dr P-Mathew Nebu 2011/05/20		projection 	MM ←→	size A4	scale 2:1
tolerance std ISO 406 ISO 1101		eng Narayanan, Aru 2021/02/03				ecn no ELX-I-39903-1	
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr -				rel level Released	
surface 3.200		appr Kuriakose, San 2021/02/03		product family METRAL 1000/2000		rev	
linear	0.X	±0.3	Amphenol FCi	title VERTICAL SIGNAL HDR SHROUD		84620	
	0.XX	±0.13		5 ROW, PRESS-FIT, STANDARD		E	
angular	0°	±2°		cat. no. -		Product - Customer Drw	
ISO 1302		amphenol-icc.com		sheet 1 of 1			