

 REVISIONS

 REV
 ECO
 DESCRIPTION
 DATE
 BY
 APPR

 A1
 —
 RELEASE NEW DRAWING
 01/APR/22
 IAN
 TOMMY

SIZE 12 CONTACTS
(4 PLACES)

SIZE 16 CONTACTS
(23 PLACES)

7

SIZE 16 CONTACTS
(23 PLACES)

7

Proposition of the contact of t

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

 $\hbox{HOUSING: THERMOPLASTIC; BLACK}$

SEAL: SILICONE RUBBER

THREADED INSERT: STAINLESS STEEL

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA);

REDUCED DIA. WIRE SEAL; SEALED PANEL MOUNT


3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
- 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);

IP69K(MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-27S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6. RECEPTACLE IS SUPPLIED WITH DUST CAP (NOT SHOW)




RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM

7 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
16	1.35 mm (.053 in)	2.62 mm (.103 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS
12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS



	AHDP02-24-27PR-BRA		-BRA							9	
QUANTITY	PART NUMBER		٦	DESCRIPTION				ITEM	่ ⊸		
MATERIALS LIST											
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE	Amphonol					1	
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		DRAWN:	IAN.XIAO	Ampher On On Onlaprice							
2 PL DEC ±0.15 3 PL DEC ±0.08	Fractions ±1/64 Angles ±1°							henol-sine.com			
3) Note reference :	- X	ENGINEER:	ER:		44724 Morley Drive						
MATERIAI SPECIFICA	TIONS:	APPROVAL:	TOMMY.XIE	06/APR/22		Clinton Township, MI 48036				4	
WEIGHT:63.5g		CUSTOMER:		27POS,RECEPTACLE,PIN,24SZ,							
		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY, DESIGN FEATURES.		RD SEAL,BRA,PANELMATE AHDP							
PROCESS SPECIFICAT	FIONS:	SPECIFICATIONS AND PERFORMAN SHOWN HEREON ARE THE PROPER THE AMPHENOL CORPORATION. NO OF REPRODUCTION ARE IMPLIED. A DIMENSIONS ARE SUBJECT TO NOR MANUFACTURING VARIATIONS.		RMANCE DATA OPERTY OF IN. NO RIGHTS IED. ALL	B	C-	AHDP02-24	27PR-BRA	A1		
NEXT ASS'Y:				S.	SCALE: N	IONE	DURAMATE	sнеет 1 о	F 1	1	