




Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Receptacle**

Connector System: **Board-to-Board**

Termination Post & Tail Length: **4 mm [.157 in]**

Number of Positions: **128**

Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Expanded
DIN Level	II

Configuration Features

Mating & Unmating Configuration	Normal
Number of Positions	128
Number of Rows	4
PCB Mount Orientation	Vertical
Number of Columns	32
Number of Signal Positions	128
Rows Loaded	Fully Loaded

Contact Features

--	--



Contact Type	Receptacle
--------------	------------

Contact Base Material	Copper Alloy
-----------------------	--------------

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Termination Post & Tail Length	4 mm[.157 in]
--------------------------------	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	PBT GF30
------------------	----------

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Connector Length	95 mm
------------------	-------

Connector Height	13.2 mm
------------------	---------

Connector Width	11.6 mm
-----------------	---------

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Approved Standards Products	UL E84703
---	-----------

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
--	---

Halogen Content Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 364918-E STVCD 128 M ABCD VVV 4-00 0606 * * 247</p>	 <p>TE Part # 384283-E STVCD 128 M ABCD VVV 4-00 0606 * * 137</p>	 <p>TE Part # 384671-E STVCD 128 M ABCD VVV 4-00 EE ** 247 E0</p>	 <p>TE Part # 484822-E STVCD 128 M ABCD VVV 4-00 0606 * 8360 2</p>
--	--	--	---

Customers Also Bought

 <p>TE Part #1-1734580-1 MOD-Jack,RJ45, 10P10C, SHD LP, 6u" Au</p>	 <p>TE Part #SRK15MDA32A001G003 HDR, 32P, BLK, ST, AU/NI/CU, A</p>	 <p>TE Part #214915-E MSPPM 5 F SMDTHR F10 * A V 137 094 * E00</p>	 <p>TE Part #280370-3 2P AMPMODU II SHRD HDR, ST, 0.76 AU</p>
 <p>TE Part #364918-E STVCD 128 M ABCD VVV 4-00 0606 * * 247</p>	 <p>TE Part #374463-E STVRD 128 MI ABCD VVV 4-00 GA06 4,0 * 2</p>	 <p>TE Part #384307-E STVE 160 M ABCDE VVVV 4-00 EE ** 247 E</p>	 <p>TE Part #594750-E STVH15 15 F ZD W 2 1206 4,3 * 197 E 172</p>



Documents

Product Drawings

[STVCD 128 F ABCD VVV 7-00 TL 4,0 * 247](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_254977-E_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_254977-E_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_254977-E_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English