



ELECTRICAL SPECIFICATIONS :

- Frequency range : 758 to 803 MHz
- Input power : 130 W
- Input power, peak : 1300 W
- Reflected power : 80 W
- Isolation (within frequency range, port 2 to 1) : 22 dB Min
- Return Loss (Measured at port 1 and port 2) : 23 dB Min (0°C-115°C)
 (Measured at port 1 and port 2) : 20 dB Min (-40°C-0°C)
- Insertion Loss (within frequency range, port 1 to 2) : 0.25 dB Max
- Intermodulation distortion, IM3(2 x 50 W) : -65 dBc Max
 IM5(2 x 50 W) : -79 dBc Max
- Harmonics: 2 x f(100W CW) : 0dBm Max
 3-4 x f (100W CW) : -10 dBm Max
 5 x f (100W CW) : -35dBm Max
 6-7 x f (100W CW) : -25 dBm Max
- Operating temperature range: -40°C to +115°C
- Storage temperature range : -40°C to +115°C
- Direction : CW

BODY: STEEL, SILVER PLATED
 RIGID PINS: COPPER, SILVER PLATED
 NOTES:

1. STANDARD INPUT/OUTPUT IMPEDANCE 50 Ohm.
2. LEAD FREE, NO Nd MATERIAL, BeO FREE.
3. THE DIMENSION OF THE DATA MATRIX IS 7.6MM*7.6MM, INFORMATION INCLUDED WORK ORDER NUMBER-SERIAL NUMBER-MATERIAL NUMBER
4. THIS PART COMPLIES WITH ALL ROHS REQUIREMENTS

ENG PART#: 801-075-080-WB040

FUNCTIONAL SYMBOLS F=0 F=0 F=0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: CHANGE ECTR RESTRICTED ***		molex		
	DIMENSION UNITS MM	SCALE 1:1	EC NO: 702316				
	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: SREN05	2022/04/20			
			CHK'D: WWANG99	2022/04/21			
DIVISIONAL SYMBOLS			APPR: HWANG186	2022/04/22	PRODUCT CUSTOMER DRAWING		
	4 PLACES ±0.005 ±----		INITIAL REVISION:				
	3 PLACES ±0.025 ±----		DRWN: SREN05	2021/12/08			
	2 PLACES ±0.13 ±----		APPR: HWANG186	2022/03/01			
1 PLACE ±0.25 ±----		ANGULAR TOL ± 1.5 °		DOCUMENT NUMBER 735912095	DOC TYPE PSD		
0 PLACES ±0.4 ±----		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DOC PART 000	REVISION A1		
		THIRD ANGLE PROJECTION	DRAWING A3-SIZE	SERIES 73591	MATERIAL NUMBER 0735912095	CUSTOMER GENERAL MARKET	SHEET NUMBER 1 OF 1