

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 2018

BY TE CONNECTIVITY CORPORATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-17-004116	23MAR2017	DR	DR
	A1	ECO-18-011024	11JUL2018	DR	DR
	A2	ECO-18-017177	30OCT2018	DR	DR
	A4	REV PER ECN-22-188519	06DEC2022	SMR	PK

0.20  
D 2 SURFACES

2.50

42.4

15.00

5.00

18.0

4.00

4.00

23.0

6.50

6.50

35.00

2X 16.0

3

D1

D2

D3

D4

D5

D6

D7

D8

D9

(4X R3.0)

(45°)

RECESSED HORIZONTAL PATTERN

A2

SECTION C-C  
SCALE 5:1

2840393-2

1 MATERIAL: C11000 H02

2 PLATING: 0.0030-0.0050 SILVER PER ASTM B 700, TYPE 3, CLASS N, WITHOUT SUPPLEMENTARY CHROMATE TREATMENT BUT WITH A TARNISH RESISTANT TREATMENT, OVER 0.0010-0.0020 MATTE NICKEL

3 DIMENSION TO THEORETICAL SHARP CORNER

SUPERSEDED BY 2840393-1	TAB CONTACT WITH KNURL	A	2840393-2
	TAB CONTACT	A	2840393-1
	DESCRIPTION	REV	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 16AUG2016

CHK D. RHEIN 24AUG2016

APVD D. RHEIN 24AUG2016

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 18.0 g

CUSTOMER DRAWING

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.2
2 PLC	±0.10
3 PLC	±0.050
4 PLC	±
ANGLES	±2°

MATERIAL

1

FINISH

2

NAME

D. RHEIN

D. RHEIN

D. RHEIN

-

-

-

-

TAB CONTACT  
HC-STAK 25 PLUG

SIZE

A300779

CAGE CODE

C-2840393

DRAWING NO

-

RESTRICTED TO

-

SCALE

2:1

SHEET

1 OF 1

REV

A4

1470-19 (3/13)

TE Connectivity