


ITEM	PART#	DESCRIPTION	QTY	UOM
A,B	5023800600	1.25 W/B Single Plg Hsg 6Ckt	2	PC
C	5023810000	1.25 W/B Single Plg Term W/Pit	12	PC
D	--	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	B1	1X26AWG DISC BK	BLACK
A2	B2	1X26AWG DISC BK	BLACK
A3	B3	1X26AWG DISC BK	BLACK
A4	B4	1X26AWG DISC BK	BLACK
A5	B5	1X26AWG DISC BK	BLACK
A6	B6	1X26AWG DISC BK	BLACK



MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
3. LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
4. LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	B	INITIAL RELEASE	THANUB

RELEASE STATUS	P1	RELEASE DATE	2023/05/05	16:46:44
----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS $\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$ DIVISIONAL SYMBOLS	DIMENSION UNITS: mm SCALE: NTS GENERAL TOLERANCES (UNLESS SPECIFIED): ANGULAR TOL: ± ° 4 PLACES: ± 3 PLACES: ± 2 PLACES: ± 1 PLACE: ± 0 PLACES: ±	CURRENT REV DESC: EC NO: 745876 DRWN: THANUB 2023/04/11 CHK'D: RDOMZALS 2023/05/05 APPR: RDOMZALS 2023/05/05							
	INITIAL REVISION: DRWN: THANUB 2023/01/15 APPR: SKUMAR07 2023/02/06					PRODUCT CUSTOMER DRAWING			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING: A4-SIZE	SERIES: 224091	DOCUMENT NUMBER: 2240911060	DOC TYPE: PSD	DOC PART: 000	REVISION: B
				MATERIAL NUMBER: SEE TABLE	CUSTOMER: GENERAL MARKET	SHEET NUMBER: 1 OF 1			