

Standard MOV Varistor

Square, 25mm

multicomp PRO

**RoHS
Compliant**



Description

Metal Oxide Varistor (MOV) as one nonlinear resistance element is mainly made of zinc oxide (ZnO), which has very high surge capacity and big nonlinear coefficient. Below the threshold voltage, its resistance is very high, nearly no current flows through, but above the threshold voltage, the resistance reduces sharply, huge current can be discharged. Due to this characteristic, varistor as a protection component in electronic and electrical equipment can absorb abnormal over-voltage and lightning surge.

Varistor is with High Surge Current Density, Low Clamping Voltage, and Good Surge Capacity.


Applications

- Power Supplies
- Home Electrical Appliances
- Industrial Devices
- Surge Protectors
- Telecom Devices


Features

- Epoxy Resin Coating
- Silicone Resin Coating
- Low Leakage Current
- Bidirectional and Symmetrical V/I Characteristics
- Operating Temperature Range
- Low Temperature: -40°C
- High Temperature: +85°C to +105°C

Product Structure



Temp. Derating Curve



For Normal Temp. Series

Note:

When ambient Temp. exceeds 85°C, the peak surge current and energy rating should be reduced as shown in the left curve.


Standard MOV Varistor Square, 25mm

multicomp PRO

General Technical Data

Item	Value	Unit
Operating Temperature	-40 to +85	°C
Storage Temperature	-40 to +125	°C
Voltage Proof	≥2500	Vac
Insulation Resistance	≥100	MΩ

Dimensions



Model	L	W (Max.)	W1	W2	H (Max.)	H1	T (Max.)	T1	d	F	F1
MPV25S241KNK	12 ±3	28	4 ±0.05	2 ±0.05	30	2 ±0.05	4.6	0.5 ±0.05	2.5 ±0.05	18 ±0.6	1.4 - 2.9
MPV25S431KNK							5.8				2 - 4

Specification

Model	Max. Continuous Operating Voltage		Varistor Voltage @1 mA DC		Clamping Voltage (Max.)		Max. Discharge Current (8/20 μs)		Max. Energy (10/1000 μs)	Typical Capacitance (For reference only) @1 kHz	Agency Approvals			
	Vac	Vdc	Min.	Max.	VC	IP	In	I _{max}	(J)	(pF)	UL	cUL	TUV	CQC
	(V)	(V)	(V)	(V)	(V)	(V)	(kA)				•	•	•	○
MPV25S241KNK	150	200	216	264	395	175	10	25	302	2800	•	•	•	○
MPV25S431KNK	275	350	387	473	710				575	1600	•	•	•	○

• : Approved ○ : Unauthorized

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro


multicomp PRO

Standard MOV Varistor

Square, 25mm

Performance Curve

Max. Peak Current Derating Curves



Part Number Table

Description	Part Number
Varistor, 240V	MPV25S241KNK
Varistor, 430V	MPV25S431KNK

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.