


**OMNIMATE Signal - series BL/SL 5.08**  
**BLZ 5.08/06/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Do not use product for new developments**



Female plugs with clamping-yoke screw for wire connection with straight (180°) outlet direction. The female plugs provide space for labelling and can be coded.

**General ordering data**

|                     |                                                                                                                                    |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Delivery status     | <b>This article will no longer be available in the future.</b>                                                                     |
| Available until     | 2019-12-31                                                                                                                         |
| Type                | BLZ 5.08/06/180 SN BK BX                                                                                                           |
| Order No.           | <a href="#">1526810000</a>                                                                                                         |
| Version             | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 6, 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², Box |
| GTIN (EAN)          | 4008190163891                                                                                                                      |
| Qty.                | 50 pc(s).                                                                                                                          |
| Product data        | IEC: 400 V / 19 A / 0.2 - 2.5 mm²<br>UL: 300 V / 15 A / AWG 26 - AWG 12                                                            |
| Packaging           | Box                                                                                                                                |
| Alternative product | <a href="#">1943850000</a>                                                                                                         |

## OMNIMATE Signal - series BL/SL 5.08 BLZ 5.08/06/180 SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Technical data

#### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 9.98 g |
|------------|--------|

#### System parameters

|                                            |                                     |                                              |                          |
|--------------------------------------------|-------------------------------------|----------------------------------------------|--------------------------|
| Product family                             | OMNIMATE Signal - series BL/SL 5.08 | Wire connection method                       | Clamping yoke connection |
| Pitch in mm (P)                            | 5.08 mm                             | Pitch in inches (P)                          | 0.2 inch                 |
| Conductor outlet direction                 | 180°                                | No. of poles                                 | 6                        |
| L1 in mm                                   | 25.4 mm                             | L1 in inches                                 | 1 inch                   |
| Number of rows                             | 1                                   | Pin series quantity                          | 1                        |
| Rated cross-section                        | 2.5 mm <sup>2</sup>                 | Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch   |
| Touch-safe protection acc. to DIN VDE 0470 | IP 20                               | Volume resistance                            | 4.50 mΩ                  |
| Can be coded                               | Yes                                 | Stripping length                             | 7 mm                     |
| Tightening torque, min.                    | 0.4 Nm                              | Tightening torque, max.                      | 0.5 Nm                   |
| Clamping screw                             | M 2.5                               | Screwdriver blade                            | 0.6 x 3.5                |
| Screwdriver blade standard                 | DIN 5264                            | Plugging cycles                              | 25                       |
| push-in force/pole                         | 10 N                                | Withdrawal force per pole                    | 8 N                      |
| Packaging                                  | Box                                 |                                              |                          |

#### Material data

|                                       |                          |                                       |                     |
|---------------------------------------|--------------------------|---------------------------------------|---------------------|
| Insulating material                   | PBT                      | Colour                                | Black               |
| Colour chart (similar)                | RAL 9011                 | Insulating material group             | IIIa                |
| CTI                                   | ≥ 200                    | Insulation resistance                 | ≥ 10 <sup>8</sup> Ω |
| UL 94 flammability rating             | V-0                      | Contact base material                 | Copper alloy        |
| Contact material                      | Copper alloy             | Contact surface                       | tinned              |
| Layer structure of plug contact       | 4-8 µm Sn hot-dip tinned | Storage temperature, min.             | -25 °C              |
| Storage temperature, max.             | 55 °C                    | Max. relative humidity during storage | 80 %                |
| Operating temperature, min.           | -50 °C                   | Operating temperature, max.           | 100 °C              |
| Temperature range, installation, min. | -25 °C                   | Temperature range, installation, max. | 100 °C              |

#### Conductors suitable for connection

|                                                 |                         |                                                 |                      |
|-------------------------------------------------|-------------------------|-------------------------------------------------|----------------------|
| Clamping range, min.                            | 0.13 mm <sup>2</sup>    | Clamping range, max.                            | 3.31 mm <sup>2</sup> |
| Wire connection cross section AWG, min.         | AWG 26                  | Wire connection cross section AWG, max.         | AWG 12               |
| Solid, min. H05(07) V-U                         | 0.2 mm <sup>2</sup>     | Solid, max. H05(07) V-U                         | 2.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                      | 0.2 mm <sup>2</sup>     | Flexible, max. H05(07) V-K                      | 2.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.2 mm <sup>2</sup>     | w. plastic collar ferrule, DIN 46228 pt 4, max. | 2.5 mm <sup>2</sup>  |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 0.2 mm <sup>2</sup>     | w. wire end ferrule, DIN 46228 pt 1, max.       | 2.5 mm <sup>2</sup>  |
| Plug gauge acc. to EN 60999 a x b; Ø            | 2.8 mm x 2.0 mm; 2.4 mm |                                                 |                      |

**OMNIMATE Signal - series BL/SL 5.08**  
**BLZ 5.08/06/180 SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Rated data acc. to IEC**

tested acc. to standard

IEC 60664-1, IEC 61984

 Rated current, max. no. of poles  
 (Tu=20°C)

14.5 A

 Rated current, max. no. of poles  
 (Tu=40°C)

12.5 A

 Rated voltage for surge voltage class /  
 pollution degree III/2

320 V

 Rated impulse voltage for surge voltage  
 class/ pollution degree II/2

4 kV

 Rated impulse voltage for surge voltage  
 class/ contamination degree III/3

4 kV

 Rated current, min. no. of poles  
 (Tu=20°C)

19 A

 Rated current, min. no. of poles  
 (Tu=40°C)

16 A

 Rated voltage for surge voltage class /  
 pollution degree II/2

400 V

 Rated voltage for surge voltage class /  
 pollution degree III/3

250 V

 Rated impulse voltage for surge voltage  
 class/ pollution degree III/2

4 kV

Short-time withstand current resistance

3 x 1s with 120 A

**Rated data acc. to CSA**

Institute (CSA)



Certificate No. (CSA)

200039-1121690

Rated voltage (Use group B)

300 V

Rated current (use group B)

15 A

Wire cross-section, AWG, min.

AWG 26

Reference to approval values

 Specifications are  
 maximum values, details -  
 see approval certificate.

Rated voltage (use group D)

300 V

Rated current (use group D)

10 A

Wire cross-section, AWG, max.

AWG 12

**Rated data acc. to UL 1059**

Institute (UR)



Certificate No. (UR)

E60693

Rated voltage (use group B)

300 V

Rated current (use group B)

15 A

Wire cross-section, AWG, min.

AWG 26

Reference to approval values

 Specifications are  
 maximum values, details -  
 see approval certificate.

Rated voltage (use group D)

300 V

Rated current (use group D)

10 A

Wire cross-section, AWG, max.

AWG 12

**Classifications**

ETIM 3.0

EC001284

ETIM 5.0

EC002637

UNSPSC

30-21-18-10

eClass 6.2

27-26-07-04

eClass 8.1

27-44-04-02

eClass 9.1

27-44-04-02

ETIM 4.0

EC002637

ETIM 6.0

EC002637

eClass 5.1

27-26-07-04

eClass 7.1

27-44-04-02

eClass 9.0

27-44-04-02

## OMNIMATE Signal - series BL/SL 5.08 BLZ 5.08/06/180 SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Notes

#### Notes

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

#### IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

### Approvals

#### Approvals



#### ROHS

Conform

### Downloads

#### Approval/Certificate/Document of Conformity

[Declaration of the Manufacturer](#)

#### Brochure/Catalogue

[FL DRIVES EN](#)  
[MB DEVICE MANUF. EN](#)  
[FL DRIVES DE](#)  
[FL BUILDING SAFETY EN](#)  
[FL APPL LED LIGHTING EN](#)  
[FL INDUSTR.CONTROLS EN](#)  
[FL MACHINE SAFETY EN](#)  
[FL HEATING ELECTR EN](#)  
[FL APPL INVERTER EN](#)  
[FL\\_BASE\\_STATION\\_EN](#)  
[FL ELEVATOR EN](#)  
[FL POWER SUPPLY EN](#)  
[FL 72H SAMPLE SER EN](#)  
[PO OMNIMATE EN](#)

### OMNIMATE Signal - series BL/SL 5.08 BLZ 5.08/06/180 SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensional drawing

