



MODEL 44011

Precision Epoxy NTC Thermistor

- 100,000 ohm Resistance @ 25°C
- Interchangeable $\pm 0.2^\circ\text{C}$, 0°C to 70°C
- Pressed Disk Ceramic Sensor
- High sensitivity
- Thermally conductive epoxy coating
- 0.095" (2.4 mm) Maximum Diameter
- 32 AWG, 3" (7.6 cm) long Silver plated copper leads
- RoHS Compliant

FEATURES

- 100,000 Ohm Resistance @ 25°C
- Interchangeability
- Good Long Term Stability
- High Sensitivity
- Thermally Conductive Epoxy Coating
- RoHS Compliance

APPLICATIONS

- High-range Temperature Applications
- Tight Tolerance Instrumentation
- General Applications Requiring Stability
- Applications Requiring Sensing Small Changes in Temperature
- Non-condensing Moisture Environments
- Allows use in Applications World-wide


MODEL 44011

Precision Epoxy NTC Thermistor

PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C	Ohms	100,000
Tolerance 0°C to 70°C	°C	± 0.2
Beta Value 25/85	K	4144
Tolerance on Beta Value	%	0.8
Time response in air	Seconds	< 10
Dissipation Constant in air	mW/°C	1
Insulation Resistance (Min. of 100 Mohms for 1 sec.)	Volts	500

MECHANICAL DETAILS



TYPICAL PERFORMANCE CURVES (RESISTANCE OF INDIVIDUAL THERMISTORS)

Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms
-40	3356	0	333.1	40	52.19	80	11.54	120	3.307
-39	3147	1	316.4	41	50.07	81	11.15	121	3.214
-38	2951	2	300.6	42	48.04	82	10.78	122	3.124
-37	2769	3	285.7	43	46.11	83	10.42	123	3.038
-36	2599	4	271.6	44	44.26	84	10.08	124	2.953
-35	2440	5	258.3	45	42.50	85	9.744	125	2.872
-34	2292	6	245.7	46	40.81	86	9.424	126	2.793
-33	2154	7	233.8	47	39.20	87	9.117	127	2.717
-32	2025	8	222.5	48	37.66	88	8.821	128	2.643
-31	1904	9	211.9	49	36.19	89	8.536	129	2.571
-30	1791	10	201.7	50	34.78	90	8.261	130	2.501
-29	1685	11	192.2	51	33.44	91	7.996	131	2.434
-28	1586	12	183.1	52	32.15	92	7.741	132	2.369
-27	1494	13	174.5	53	30.92	93	7.496	133	2.306
-26	1407	14	166.3	54	29.74	94	7.259	134	2.244
-25	1326	15	158.6	55	28.61	95	7.030	135	2.185
-24	1250	16	151.3	56	27.53	96	6.810	136	2.128
-23	1178	17	144.3	57	26.50	97	6.598	137	2.072
-22	1111	18	137.7	58	25.50	98	6.393	138	2.018
-21	1049	19	131.4	59	24.56	99	6.195	139	1.965
-20	989.8	20	125.5	60	23.65	100	6.005	140	1.914
-19	934.6	21	119.8	61	22.77	101	5.821	141	1.865
-18	882.7	22	114.5	62	21.94	102	5.643	142	1.817
-17	834.0	23	109.4	63	21.14	103	5.472	143	1.770
-16	788.2	24	104.5	64	20.37	104	5.307	144	1.725
-15	745.2	25	100.0	65	19.63	105	5.147	145	1.681
-14	704.7	26	95.51	66	18.93	106	4.993	146	1.639
-13	666.7	27	91.34	67	18.25	107	4.844	147	1.598
-12	630.9	28	87.38	68	17.60	108	4.700	148	1.558
-11	597.2	29	83.60	69	16.97	109	4.561	149	1.519
-10	565.5	30	80.00	70	16.37	110	4.427	150	1.481
-9	535.6	31	76.58	71	15.80	111	4.297		
-8	507.5	32	73.32	72	15.25	112	4.172		
-7	481.0	33	70.22	73	14.72	113	4.051		
-6	456.0	34	67.26	74	14.21	114	3.933		
-5	432.4	35	64.44	75	13.72	115	3.820		
-4	410.2	36	61.75	76	13.25	116	3.711		
-3	389.2	37	59.19	77	12.79	117	3.605		
-2	369.4	38	56.75	78	12.36	118	3.502		
-1	350.7	39	54.42	79	11.94	119	3.403		

MODEL 44011

Precision Epoxy NTC Thermistor

ORDERING INFORMATION

Part Number	Description	Ω @25°C
701011	44011RC, THERMISTOR, ROHS COMPLIANT	100,000
701111	44011RC-BP (100 PCS), THERMISTOR, ROHS	100,000

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Tel: 800-440-5100
customercare.tlse@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.