
PCB terminal block; 6 mm²; Pin spacing 12.5 mm; 9-pole; Push-in CAGE

CLAMP®; 6,00 mm²; gray

www.wago.com/2626-3359








 $\label{thm:continuity} \textbf{Subject to changes. Please also observe the further product documentation!}$

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com





Item description

- PCB terminal strips with Push-in CAGE CLAMP® connection
- Push-in termination of solid and ferruled conductors
- Ideal for panel feedthrough applications via operation parallel to conductor entry
- Testing can be performed both parallel and perpendicular to conductor entry

Data Electrical data

Ratings per IEC/EN 60664-1

Ratings per	IEC/EN 60664-1
Nominal voltage (III/3)	1000 V
Rated surge voltage (III/3)	8kV
Rated voltage (III/2)	1000 V
Rated surge voltage (III/2)	8kV
Nominal voltage (II/2)	1000 V
Rated surge voltage (II/2)	8kV

 $\label{thm:continuity} \textbf{Subject to changes. Please also observe the further product documentation!}$

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/2626-3359



Rated current	48 A
Legend (ratings)	(III / 2) ≙ Overvoltage category III / Pollution degree 2

Approvals per UL 1059

Rated voltage UL (Use Group B)	600 V
Rated current UL (Use Group B)	38 A
Rated voltage UL (Use Group C)	600 V
Rated current UL (Use Group C)	38 A

Connection data

Connection technology	Push-in CAGE CLAMP®
Actuation type	Operating tool
Solid conductor	0,2 10 mm² / 24 8 AWG
Fine-stranded conductor	0,2 10 mm² / 24 8 AWG
Fine-stranded conductor; with insulated ferrule	0,25 6 mm²
Fine-stranded conductor; with uninsulated ferrule	0,25 6 mm²
Fine-stranded conductor; with twin ferrule	0,25 2,5 mm²
Strip length	13 15 mm / 0.51 0.59 inch
Conductor connection direction to PCB	90°
Pole No.	9
Total number of connection points	9
Total number of potentials	9
Number of connection types	1
Number of levels	1

Geometrical Data

Pin spacing	12,5 mm / 0.492 inch
Width	109,3 mm / 4.303 inch
Height	28,2 mm / 1.11 inch
Height from the surface	24,2 mm / 0.953 inch
Depth	18,5 mm / 0.728 inch
Solder pin length	4 mm
Solder pin dimensions	1,5 x 1 mm
Drilled hole diameter with tolerance	2 ^(+0,1) mm

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/2626-3359



Mechanical data

Mounting type	Feed-through mounting	
PCB contact		
PCB contact	ТНТ	
Solder pin arrangement	over the entire terminal strip (in-line)	
Number of solder pins per potential	2	

Material Data

Color	gray
Material group	1
Insulation material	Polyamide 66 (PA 66)
Flammability class per UL94	VO
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E _{Cu})
Contact plating	tin-plated
Weight	47.7 g

Environmental Requirements

Limit temperature range	-60 +105 °C
-------------------------	-------------

Commercial data

Packaging type	BOX
Country of origin	PL
GTIN	4055143898027
Customs tariff number	85369010000

Approvals / Certificates

Country specific Approvals

			Certificate
Logo	Approval	Additional Approval Text	name
	CSA	C22.2	70146882
DEKRA Certification B.V.			

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/2626-3359





KEMA/KEUR DEKRA Certification B.V. EN 60947-7-4

71-107864

Counterpart

Downloads

Documentation

Additional Information

Technical explanations Apr 3, 2019 pdf Download 3.6 MB

CAD/CAE-Data

PCB Design

Symbol and Footprint 2626-3359

URL Download

CAx data for your PCB design, consisting of "schematic symbols and PCB footprints", allow easy integration of the WAGO component into your development environment.

Supported formats:

- Accel EDA 14 & 15
- Altium 6 to current version
- Cadence Allegro
- DesignSpark
- **Eagle Libraries**
- KiCad
- Mentor Graphics BoardStation
- Mentor Graphics Design Architect
- Mentor Graphics Design Expedition 99 and 2000
- OrCAD 9.X PCB and Capture
- PADS PowerPCB 3, 3.5, 4.X, and 5.X
- PADS PowerPCB and PowerLogic 3.0
- PCAD 2000, 2001, 2002, 2004, and 2006
- Pulsonix 8.5 or newer
- STL
- 3D STEP

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

03.06.2020 Page 5/6

www.wago.com/2626-3359



- TARGET 3001!
- View Logic ViewDraw
- Quadcept
- Zuken CadStar 3 and 4
- Zuken CR-5000 and CR-8000

PCB Component Libraries (EDA), PCB CAD Library Ultra Librarian

Handling Instructions

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.