


Terminal Strips with Fixing Flanges or Snap-in Mounting Feet, Series 261



Side-entry

CAGE CLAMP®




<p>0.08 – 2.5 mm² AWG 28 – 14 500 V/6 kV/3 ① 300/600 V, 15/5 A ② 24 A 300/600 V, 20/5 A ③</p> <p>Pole width 6 mm / 0.236 in 8 – 9 mm / 0.33 in</p>	<p>2 x 0.08 – 2.5 mm² 2 x AWG 28 – 14 500 V/6 kV/3 ① 300/600 V, 15/5 A ② 24 A 300/600 V, 20/5 A ③</p> <p>Pole width 10 mm / 0.394 in 8 – 9 mm / 0.33 in</p>
<p>* VDE KEMA CCA SABS ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲ ⑳ ㉑ ㉒ ㉓ ㉔ ㉕ ㉖ ㉗ ㉘ ㉙ ㉚ ㉛ ㉜ ㉝ ㉞ ㉟ ㊱ ㊲ ㊳ ㊴ ㊵ ㊶ ㊷ ㊸ ㊹ ㊺ ㊻ ㊼ ㊽ ㊾ ㊿</p>	<p>* VDE KEMA CCA SABS ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲ ⑳ ㉑ ㉒ ㉓ ㉔ ㉕ ㉖ ㉗ ㉘ ㉙ ㉚ ㉛ ㉜ ㉝ ㉞ ㉟ ㊱ ㊲ ㊳ ㊴ ㊵ ㊶ ㊷ ㊸ ㊹ ㊺ ㊻ ㊼ ㊽ ㊾ ㊿</p>


- ① 500 V = rated voltage
6 kV = rated surge voltage
3 = pollution degree
(see also section 10)
- ② For longer strips and/or assemblies of different colors, please contact factory
- ③ Suitable for EEx i applications with blue insulating housings



Description



Terminal strips with fixing flanges, for screw fixing or similar methods, fixing hole diameter 3.2 mm (with mounting adapter 209-123 also for DIN 35 rail)



Terminal strips with snap-in mounting feet, for plate thickness 0.6 – 1.2 mm, fixing hole diameter 3.5 mm (fits aluminum rail 210-154 or with mounting adapter 209-120 for DIN 35 rail)



Description	No. of poles	Item-No.	Pack.-unit pcs	No. of poles	Item-No.	Pack.-unit pcs
2-conductor terminal strips with fixing flanges, grey				4-conductor terminal strips with fixing flanges, grey		
2	261-102	100	2	261-202	100	
3	261-103	100	3	261-203	100	
4	261-104	100	4	261-204	100	
5	261-105	100	5	261-205	100	
6	261-106	50	6	261-206	50	
7	261-107	50	7	261-207	50	
8	261-108	50	8	261-208	50	
9	261-109	50	9	261-209	50	
10	261-110	25	10	261-210	25	
11	261-111	25	11	261-211	25	
12 ②	261-112	25	12 ②	261-212	25	
2-conductor terminal strips with snap-in mounting feet, grey				4-conductor terminal strips with snap-in mounting feet, grey		
2	261-152	100	2	261-252	100	
3	261-153	100	3	261-253	100	
4	261-154	100	4	261-254	100	
5	261-155	100	5	261-255	100	
6	261-156	50	6	261-256	50	
7	261-157	50	7	261-257	50	
8	261-158	50	8	261-258	50	
9	261-159	50	9	261-259	50	
10	261-160	25	10	261-260	25	
11	261-161	25	11	261-261	25	
12 ②	261-162	25	12 ②	261-262	25	

Dimensions for modular terminal blocks and terminal strips (in mm)

Modular terminal blocks and terminal strips with fixing flanges

L = No. of poles x pole width
L₁ = L + 8.1 mm
L₂ = L + 14.5 mm



Additional item-Nos. for colored terminal strips
blue .../000-006 ①



Modular terminal blocks and terminal strips with snap-in mounting feet


③ End terminal block; see page 1.18.

L = (No. of poles x pole width) + 4.4 mm



Terminal Strips, with Push Buttons on One or Both Sides, with Fixing Flanges or Snap-in Mounting Feet, Series 261

CAGE CLAMP®



Side-entry

0.08 – 2.5 mm² | AWG 28 – 14
500 V/6 kV/3 ①
24 A

Pole width 6 mm / 0.236 in
8 – 9 mm / 0.33 in



*CNET

2 x 0.08 – 2.5 mm² | 2 x AWG 28 – 14
500 V/6 kV/3 ①
24 A


Pole width 10 mm / 0.394 in
8 – 9 mm / 0.33 in

*CNET

- ① 500 V = rated voltage
6 kV = rated surge voltage
3 = pollution degree
(see also section 10)
- ② For longer strips and/or assemblies of different colors, please contact factory
- ③ For item-No. and packing-unit, see page 1.19
- ④ Suitable for EEx i applications with blue insulating housings



Description



Description	No. of poles	Add. item-No. for	No. of poles	Add. item-No. for	
2-conductor terminal strips with fixing flanges, for screw fixing or similar methods, fixing hole diameter 3.2 mm (with mounting adapter 209-123 also for DIN 35 rail) with push buttons on one side, grey	2 – 12 ②	261-.../331-000 ③	4-conductor terminal strips with fixing flanges, for screw fixing or similar methods, fixing hole diameter 3.2 mm (with mounting adapter 209-123 also for DIN 35 rail) with push buttons on one side, grey	2 – 12 ②	261-.../332-000 ③
with push buttons on both sides, grey	2 – 12 ②	261-.../341-000 ③	with push buttons on both sides, grey	2 – 12 ②	261-.../342-000 ③
2-conductor terminal strips with snap-in mounting feet, for plate thickness 0.6 – 1.2 mm, fixing hole diameter 3.5 mm (fits aluminum rail 210-154 or with mounting adapter 209-120 for DIN 35 rail) with push buttons on one side, grey	2 – 12 ②	261-.../331-000 ③	4-conductor terminal strips with snap-in mounting feet, for plate thickness 0.6 – 1.2 mm, fixing hole diameter 3.5 mm (fits aluminum rail 210-154 or with mounting adapter 209-120 for DIN 35 rail) with push buttons on one side, grey	2 – 12 ②	261-.../332-000 ③
with push buttons on both sides, grey	2 – 12 ②	261-.../341-000 ③	with push buttons on both sides, grey	2 – 12 ②	261-.../342-000 ③

Modular terminal blocks and terminal strips with fixing flanges

L = No. of poles x pole width
L₁ = L + 8.1 mm
L₂ = L + 14.5 mm

Additional item-Nos. for colored terminal strips blue .../000-006 ①

Modular terminal blocks and terminal strips with snap-in mounting feet

④ End terminal block; see page 1.20

L = (No. of poles x pole width) + 4.4 mm

