

## Piezoelectric Film Sensors

Pro-Wave now presents a series of mechno-electrical sensors and detectors produced by advanced piezoelectric polymer film technology. The polymer film of polyvinylidene fluoride (PVF2) exhibits a conspicuous piezoelectric effect and also has high compliance comparing with other piezoelectric crystals or ceramic materials. Because of its superior piezoelectric strain constant (g value), 10-20 times larger than piezoelectric ceramic, it is an ideal sensing material for converting mechanical to electrical energy.


Besides the standard products shown on this catalogue, we are also developing a series of sensing devices by using this particular piezoelectric thin film material. Please contact with us for your special needs.

### Features


- High Mechno-electrical coefficient in planar, thickness and hydrostatic modes
- Low mechanical and acoustic impedance
- High resistance to moisture
- Pliant, flexible, tough and lightweight
- Self-generated voltage, non-contact, rustless, free of sparking

### Applications


- Vibration sensors and motion detectors
- Low weight accelerometers
- Pressure or force sensors
- Keyboards, keypads and touch panels
- Coin and impact sensors
- Microphones and headset speakers
- Other mechno-electrical and electro-mechanical devices



### Frequency response



### Measuring diagram



**SG:** Programmable Signal Source HP 8165A

**Amp:** Power Amplifier

**Exciter:** Exciter B&K 4809

**Acc:** Accelerometer B&K 8309

**DUT:** Device (FS-2513P) under test

**CA:** Charging Amplifier B&K 2635

**IA:** Impedance Analyzer HP4192



**S. Square Enterprise Company Limited**  
**Pro-Wave Electronics Corporation**


[Http://www.pro-wave.com.tw](http://www.pro-wave.com.tw) ; E-mail: [sales@pro-wave.com.tw](mailto:sales@pro-wave.com.tw) ; Tel: 886-2-22465101 ; Fax: 886-2-22465105

# Piezoelectric Film Sensors

## Specifications

Model Number	FS-2513P	Unit
Type	Lead Pins	-
Voltage sensitivity at fr	70	$mV/ms^{-2}$
Transverse sensitivity	10	$mV/ms^{-2}$
Resonant frequency (fr)	80±10	Hz
Capacitance	660±30%	pF@1KHz
Operation voltage (Vcc)	-	DC volts
Operation current	-	mA
Max. output current	-	mA
Operation temperature	-20 - +60	°C
Storage temperature	-40 - +70	°C

## Dimensions in mm



## Driving circuit & pin assignment of model FD-2513P

© All copyrights reserved 1994, 1998 Pro-Wave Electronics Corporation

