

## C4AQ0BU4200M1WJ

C4AQ-M, Film, Metallized Polypropylene, Automotive DC Link, 2 uF, 5%, 900 VDC, 85°C, Lead Spacing = 27.5mm



Click [here](#) for the 3D model.

### Dimensions

L	31.5mm +0.5/-0.7mm
H	20mm +0.2/-0.7mm
T	11mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	256

### General Information

Series	C4AQ-M
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Miscellaneous	Rth = 44 C/W.

### Specifications

Capacitance	2 uF
Capacitance Tolerance	5%
Voltage DC	900 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.02% (10 kHz 25C)
Insulation Resistance	15 GOhms
Max dV/dt	70 V/us
Resistance	21.9 mOhms (10kHz 70C)
Ripple Current	5.2 Amps Irms (10kHz 70C), 140 Amps Ipk
Inductance	17 nH